



Focused on you



Model: IQS5000B4H-1T



## IQCCTV 5MP 4 Camera AHD IR Bullet CCTV System, 1TB

### Kit Contents

- 4 x Dome Cameras
- 4 x 18m Plug and Play Cables
- 1 x 4 Camera DVR 1TB
- 1 x 4 Camera Power Supply

Model: IQS5000B4H-1T

#### Camera Specifications

Style	Bullet Camera
Weather Resistant	Yes (IP66)
Vandal Resistant	No
Mounting Type	Wall or Ceiling
Sensor	1/2.7" CMOS Megapixel Sensor
DSP Type	IQ5MPDSP
DSP Functions	Automatic Back-Light Compensation, Automatic White Balance, Automatic

	Electronic Shutter, UTC, Automatic Gain Control, Digital WDR
Resolution	1080P
Lens Type	Fixed
Lens Size	3.6mm
Viewing Angle	78°
Night Vision	30m IR
Minimum Illumination	0.03 Lux
Operating Voltage	12V DC
Video Output	BNC Socket
Audio Output	No
Power Input	DC Socket (2.1mm)
Operating Temperature	-30 - 55°
Dimensions	Φ69.3x150mm
Warranty	1 Year Warranty
DVR Specifications	
Video Input	4 Channel BNC / 2 IP Camera Support
Audio Input	4 Channel RCA
Video Output	VGA, HDMI
Display Split	1/4/6/SEQ
Resolution	5MP
Record Rate (Main Stream)	5MP - 12fps 4MP - 15fps 3MP - 20fps 1080P/720P/960H - 25fps
Recording Mode	Continuous/Manual/Motion
Backup Mode	Network/USB
Ethernet	RJ45 10M/100M
Wifi Connection	Yes - Optional Wifi Dongle Required (Model: WIFIDONGLE)
3G Connection	Yes - Optional 3G Dongle Required (Model: 3GDONGLE)
Internal Hard Drive	1TB
Dimensions	300x227x53mm
Warranty	1 Year Warranty