

**Order symbol:** ARK12106CHSCM  
**Product nbr:** 8561534  
**Description:** PC Enclosure  
**Remarks:** Hinged opaque screw cover, base includes 1/2 and 3/4 inch knock-outs and metal mounting feet

**EAN:** 6418074097101  
**El. number:**  
**Finland:**

Including: Hinged screw cover. Base with 10-32 brass inserts, cover with formed in place PUR gasket, stainless hinge pin and 2 cover screws. Base includes 1/2 and 3/4 inch knock-outs. Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

| Dimensions:                         |                      |       |        | Accessories:                             |                             |
|-------------------------------------|----------------------|-------|--------|--|-----------------------------|
|                                     | Length               | Width | Height |  |                             |
| mm:                                 | 305                  | 254   | 152    | ALBP1210                                 | Aluminum Back Panel         |
| inch:                               | 12.0                 | 10.0  | 6.0    | ADFP1210                                 | Dead Front Panel w/ screws  |
| <b>Materials:</b>                   |                      |       |        | ASP1210                                  | Aluminum Swing Panel        |
| <b>Material:</b>                    | Polycarbonate        |       |        | ASPK1210                                 | Swing Panel Kit incl. Panel |
| <b>Base colour:</b>                 | RAL 7035 -light grey |       |        | ASPHK12                                  | Swing Panel Kit w/o Panel   |
| <b>Cover screws material:</b>       | Stainless steel      |       |        | AMFL10                                   | 10" Mounting Flange Set     |
| <b>Cover colour:</b>                | RAL 7035 -light grey |       |        | <b>Rating:</b>                           |                             |
| <b>Gasket material:</b>             | Polyurethane         |       |        | Ingress Protection (EN 60529): IP66/IP67 |                             |
| <b>Temperatures:</b>                |                      |       |        | Impact Resistance (EN 62262): IK09       |                             |
| <b>Temperature °C (short term):</b> | -40 ... 140 °C       |       |        | Electrical insulation: Totally insulated |                             |
| <b>Temperature °C (continuous):</b> | -40 ... 80 °C        |       |        | Halogen free (DIN/VDE 0472, Part 815): 1 |                             |
| <b>Temperature °F (short term):</b> | -40 ... 284 °F       |       |        | UV resistance: UL 508                    |                             |
| <b>Temperature °F (continuous):</b> | -40 ... 175 °F       |       |        | Flammability Rating: UL 508              |                             |
| <b>Accessories:</b>                 |                      |       |        | Glow Wire Test (IEC 695-2-1) °C: 960     |                             |
| ABP1210 Painted Steel Back Panel    |                      |       |        | NEMA Class: NEMA 4, 4X, 6, 6P, 12, 13    |                             |

**Accessories:**  
 ABP1210 Painted Steel Back Panel

