

Order symbol: ARK865CHSCF
Product nbr: 8561425
Description: PC Enclosure
Remarks: Hinged opaque screw cover, base includes 1/2 and 3/4 inch knock-outs

EAN: 6418074096012
EI. number:
Finland:

Including: Hinged screw cover. Base with 10-32 brass inserts, cover with formed in place PUR gasket, stainless hinge pin and 2 cover screws. Base includes 1/2 and 3/4 inch knock-outs. Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Dimensions:			Accessories:		
	Length	Width	Height		
mm:	203	152	127	ALBP86	Aluminum Back Panel
inch:	8.0	6.0	5.0	ADFP86	Dead Front Panel w/ screws
Materials:			ASP86	Aluminum Swing Panel	
Material:	Polycarbonate		ASPK86	Swing Panel Kit incl. Panel	
Base colour:	RAL 7035 -light grey		ASPHK8	Swing Panel Kit w/o Panel	
Cover screws material:	Stainless steel		AMFL6	6" Mounting Flange Set	
Cover colour:	RAL 7035 -light grey		Rating:		
Gasket material:	Polyurethane		Ingress Protection (EN 60529): IP66/IP67		
Temperatures:			Impact Resistance (EN 62262): IK09		
Temperature °C (short term):	-40 ... 140 °C		Electrical insulation: Totally insulated		
Temperature °C (continuous):	-40 ... 80 °C		Halogen free (DIN/VDE 0472, Part 815): 1		
Temperature °F (short term):	-40 ... 284 °F		UV resistance: UL 508		
Temperature °F (continuous):	-40 ... 175 °F		Flammability Rating: UL 508		
Accessories:			Glow Wire Test (IEC 695-2-1) °C: 960		
ABP86	Painted Steel Back Panel		NEMA Class: UL Type 4, 4X, 6, 6P, 12 and 13		

