



**Order symbol:** ARK14126FSC  
**Product nbr:** 8561577  
**Description:** PC Enclosure  
**Remarks:** Opaque flat scre cover, base includes 1/2 and 3/4 inch knock-outs.

**EAN:** 6418074097538  
**El. number:**  
**Finland:**

Including: Flat screw cover. Base with 10-32 brass inserts, cover with formed in place PUR gasket and 4 stainless cover screws. Base includes 1/2 and 3/4 inch knock outs. Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting

Sample photo

Dimensions:		Length	Width	Height	Accessories:	
mm:		305	254	127	ALBP1412	Aluminum Back Panel
inch:		12.0	10.0	5.0	ADFP1412	Dead Front Panel w/ screws
<b>Materials:</b>					ASP1412	Aluminum Swing Panel
<b>Material:</b>		Polycarbonate		ASPK1412	Swing Panel Kit incl. Panel	
<b>Base colour:</b>		RAL 7035 -light grey		ASPHK14	Swing Panel Kit w/o Panel	
<b>Cover screws material:</b>		Stainless steel		AMFL12	12" Mounting Flange Set	
<b>Cover colour:</b>		RAL 7035 -light grey		<b>Rating:</b>		
<b>Gasket material:</b>		Polyurethane		Ingress Protection (EN 60529): IP66/IP67		
<b>Temperatures:</b>					Impact Resistance (EN 62262): IK09	
<b>Temperature °C (short term):</b>		-40 ... 140 °C		Electrical insulation: Totally insulated		
<b>Temperature °C (continuous):</b>		-40 ... 80 °C		Halogen free (DIN/VDE 0472, Part 815): 1		
<b>Temperature °F (short term):</b>		-40 ... 284 °F		UV resistance: UL 508		
<b>Temperature °F (continuous):</b>		-40 ... 175 °F		Flammability Rating: UL 508		
<b>Accessories:</b>					Glow Wire Test (IEC 695-2-1) °C: 960	
ABP1412		Painted Steel Back Panel		NEMA Class: NEMA 4, 4X, 6, 6P, 12, 13		
<b>Certificates:</b>					Gost R	

