



**Order symbol:** ARK864CHFLF  
**Product nbr:** 8561401  
**Description:** PC Enclosure  
**Remarks:** Hinged opaque flat cover w/Plastic quick release latch. Base includes 1/2 and 3/4 inch knock-outs and plastic mounting flanges

**EAN:** 6418074095770  
**EI. number:**  
**Finland:**

Sample photo

Including: Hinged cover. Base with 10-32 brass inserts, latched flat cover with formed in place PUR gasket, stainless hinge pin. Base with 1/2 and 3/4 inch knock-outs. Quick release latches. Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Dimensions:		Length	Width	Height	Accessories:		
mm:		203	152	101	ALBP86	Aluminum Back Panel	
inch:		8.0	6.0	4.0	ADFP86	Dead Front Panel w/ screws	
<b>Materials:</b>					ASP86	Aluminum Swing Panel	
<b>Material:</b>		Polycarbonate		ASPK86	Swing Panel Kit incl. Panel		
<b>Base colour:</b>		RAL 7035 -light grey		ASPHK8	Swing Panel Kit w/o Panel		
<b>Cover screws material:</b>		Stainless steel		AMFL6	6" Mounting Flange Set		
<b>Cover colour:</b>		RAL 7035 -light grey		<b>Rating:</b>			
<b>Gasket material:</b>		Polyurethane		Ingress Protection (EN 60529): IP66/IP67			
<b>Temperatures:</b>					Impact Resistance (EN 62262): IK09		
<b>Temperature °C (short term):</b>		-40 ... 140 °C		Electrical insulation: Totally insulated			
<b>Temperature °C (continuous):</b>		-40 ... 80 °C		Halogen free (DIN/VDE 0472, Part 815): 1			
<b>Temperature °F (short term):</b>		-40 ... 284 °F		UV resistance: UL 508			
<b>Temperature °F (continuous):</b>		-40 ... 175 °F		Flammability Rating: UL 508			
<b>Accessories:</b>					Glow Wire Test (IEC 695-2-1) °C: 960		
ABP86		Painted Steel Back Panel		NEMA Class: NEMA 4, 4X, 6, 6P, 12, 13			
<b>Certificates:</b>					Gost R		

