

SHURE[®]

LEGENDARY
PERFORMANCE™



SRH Headphones
SE Sound Isolating™ Earphones

**AUDIO ELEVATED,
EVERYWHERE.**

The full spectrum of sound.

Whether in the studio, on stage, or on the go, Shure offers a complete range of headphones and earphones for every kind of listener.

PREMIUM HEADPHONES

Perfectly suited for mastering and critical listening, Shure premium headphones deliver natural sound with unmatched nuance and detail.

STUDIO HEADPHONES

Engineered for accurate response, Shure studio headphones are ideal for both professional monitoring and personal listening.

PORTABLE HEADPHONES

Made to go anywhere, Shure portable headphones feature full, clear sound in a lightweight, foldable design that's easy to store or carry.

EARPHONES

Developed for personal monitoring, yet equally suited for personal listening, Shure sound isolating earphones deliver detailed audio while naturally blocking most background noise.



SRH1840



Professional Open Back Headphones

Designed for mastering and critical listening

PREMIUM

FEATURES

- Unparalleled acoustic performance with individually matched 40 mm neodymium drivers that deliver smooth extended highs and accurate bass
- Open-back, circumaural design for exceptionally natural sound, wide stereo image, and increased depth of field
- Unique steel driver frame design improves linearity, eliminates internal resonance, and ensures consistent performance at all volume levels
- Lightweight and durable dual-frame construction with aircraft-grade aluminum alloy yoke and stainless steel grilles for enhanced durability and hours of listening comfort

INCLUDES

- Additional pair of velour ear pads
- Dual-exit, detachable cables with MMCX connectors
- Threaded ¼" gold-plated adapter
- Zippered hard storage case



SRH1440



Professional Open Back Headphones

Designed for mastering and critical listening

PREMIUM

FEATURES

- Full-range audio with rich, controlled bass from 40 mm neodymium drivers
- Open-back, circumaural design for exceptionally natural sound, wide stereo image, and increased depth of field
- Ergonomically designed, fully adjustable, premium steel-frame padded headband for hours of listening comfort
- Impedance-optimized for direct connection to a wide range of portable audio devices

INCLUDES

- Additional pair of velour ear pads
- Dual-exit, detachable cables with MMCX connectors
- Threaded ¼" gold-plated adapter
- Zippered hard storage case



SRH1540



Premium Closed-Back Headphones

Designed for critical listening and monitoring

PREMIUM

FEATURES

- Superior acoustic performance for an expansive soundstage with clear, extended highs and warm bass
- Closed-back, circumaural design rests comfortably over the ears and reduces background noise
- Lightweight construction featuring aircraft-grade aluminum alloy yoke and carbon fiber cap for enhanced durability
- Ergonomic dual-frame, padded headband is lightweight and fully adjustable for hours of listening comfort

INCLUDES

- Additional pair of Alcantara™ ear pads
- Dual-exit, detachable cables with MMCX connectors
- Threaded ¼" gold-plated adapter
- Zippered hard storage case



SRH940



Professional Reference Headphones

Designed for critical listening, monitoring and mastering

STUDIO

FEATURES

- Accurate frequency response delivers tight bass and smooth, high-end extension, with minimal distortion
- Closed-back, circumaural design rests comfortably over the ears and reduces background noise
- Lightweight, ergonomic fit with premium padded headband for comfortable, extended wear
- Collapsible design with 90-degree swivel ear cups for easy storage and portability
- Bayonet clip securely locks detachable cable into ear cup

INCLUDES

- Additional pair of velour ear pads
- Detachable coiled and straight cables
- Threaded ¼" gold-plated adapter
- Zippered hard travel case



SRH840



Professional Monitoring Headphones Optimized for studio recording

STUDIO

FEATURES

- Tailored frequency response delivers rich bass, clear mid-range and extended highs
- Closed-back, circumaural design rests comfortably over the ears and reduces background noise
- Wide, padded headband provides ergonomic fit for superior comfort over extended periods
- Collapsible design for convenient portability
- Bayonet clip securely locks detachable cable into ear cup

INCLUDES

- Additional pair of ear pads
- Detachable coiled cable
- Threaded ¼" gold-plated adapter
- Carrying bag



SRH750DJ

Professional DJ Headphones

Engineered for live DJ mixing and monitoring

STUDIO
DJ



FEATURES

- Enhanced frequency response tuned to deliver high-output bass with extended highs
- Closed-back, circumaural design rests comfortably over the ears and reduces background noise
- Adjustable, collapsible headband with 90-degree swivel ear cups for comfort and easy one-ear placement
- Maximized power handling for DJ mixers
- Bayonet clip securely locks detachable cable into ear cup

INCLUDES

- Additional pair of ear pads
- Detachable coiled cable
- Threaded 1/4" gold-plated adapter
- Carrying bag



SRH550DJ



Professional Quality DJ Headphones

Designed for DJ mixing and personal listening

STUDIO
DJ

FEATURES

- Full-range frequency response with extended bass
- Closed-back, supra-aural design for comfortable, isolating fit
- Adjustable, collapsible headband with 90-degree swivel ear cups for comfort and flexible wearing positions
- Ultra-lightweight design folds to small size for maximum portability

INCLUDES

- Threaded ¼" gold-plated adapter
- Carrying bag



SRH440



Professional Studio Headphones

Developed for professional and home studios

STUDIO

FEATURES

- Enhanced frequency response delivers accurate audio across an extended range
- Closed-back, circumaural design rests comfortably over the ears and reduces background noise
- Optimized impedance and power handling for performance with professional audio devices
- Adjustable headband and collapsible construction provide comfort and portability
- Bayonet clip securely locks detachable cable into ear cup

INCLUDES

- Detachable coiled cable
- Threaded 1/4" gold-plated adapter
- Carrying bag



SRH240A



Professional Quality Headphones

Ideal for vivid listening on almost any device

STUDIO

FEATURES

- Wide frequency range delivers full bass and detailed highs
- Closed-back, circumaural design rests comfortably over the ears and reduces background noise
- Optimized performance for use with most pro and consumer audio devices

INCLUDES

- Threaded ¼" nickel-plated adapter



SRH145 SRH145m+



Portable Headphones

Designed for immersive listening on the go

PORTABLE

FEATURES

- Rich deep bass with full range audio
- Closed-back, on-ear design for external noise isolation and comfortable fit
- Ultra-lightweight, collapsible headband for compact carrying and storage

*Inline microphone
and three button remote
for music and calls
(SRH145m+ only)*

Made for

 iPod  iPhone  iPad



SRH144

Portable Semi-Open Headphones

Designed for detailed listening on the go

PORTABLE

FEATURES

- Extended range audio with enhanced high-frequency response
- Semi-open, on-ear design for natural sound and comfortable fit
- Ultra-lightweight, collapsible headband for compact carrying and storage





SE846



Sound Isolating™ Earphones

Extended high-end clarity + unparalleled low-end performance

SPEAKER

Quad High-Definition MicroDrivers with True Subwoofer

FEATURES

- Groundbreaking low-pass filter design enables the deep low-end performance of a True Subwoofer without sacrificing clarity or detail
- Adjustable frequency response for customized sound signatures; balanced, warm and bright options included
- Three-way system configuration for dedicated low, mid and high frequency distribution
- Detachable, Kevlar™ reinforced cable in two lengths allows for flexible wearing options and customization

INCLUDES

- Soft flex sleeves (S, M, L)
- Foam sleeves (S, M, L)
- Yellow foam sleeves
- Triple flange sleeves
- Road case
- Premium carrying case
- ¼" adapter
- Airline adapter
- Volume control
- Nozzle removal key
- 2 pairs of nozzle inserts
- Polishing cloth

- Clear
- Blue

- Bronze
- Black



SE535

Sound Isolating™ Earphones
Spacious sound + rich bass

SPEAKER

Triple High-Definition MicroDrivers

FEATURES

- Dedicated dual woofers and a single tweeter per channel for spacious soundstage and rich bass
- Internal crossover routes high and low frequencies for clarity across the audio spectrum
- Rugged and ergonomic build provides long-lasting comfort and durability for on-stage or everyday use
- Detachable, Kevlar™ reinforced cable with wireform fit for easy replacement or customization

INCLUDES

- Soft flex sleeves (S, M, L)
- Foam sleeves (S, M, L)
- Yellow foam sleeves
- Triple flange sleeves
- Premium carrying case
- ¼" adapter
- Airline adapter
- Volume control



- Metallic Bronze
- Clear



SE425

Sound Isolating™ Earphones

Accurate + balanced sound



SPEAKER

Dual High-Definition MicroDrivers

INCLUDES

- Soft flex sleeves (S, M, L)
- Foam sleeves (S, M, L)
- Yellow foam sleeves
- Triple flange sleeves
- Premium carrying case
- 1/4" adapter

- Metallic Silver
- Clear

SE315

Sound Isolating™ Earphones

Full range sound



SPEAKER

High-Definition MicroDriver + Tuned BassPort

INCLUDES

- Soft flex sleeves (S, M, L)
- Foam sleeves (S, M, L)
- Yellow foam sleeves
- Triple flange sleeves
- Carrying case

- Black
- Clear



SE215
SE215_{m+SPE}

Sound Isolating™ Earphones
Detailed sound + enhanced bass



SPEAKER
Dynamic MicroDriver

INCLUDES

- Soft flex sleeves (S, M, L)
- Foam sleeves (S, M, L)
- Carrying case



*Inline microphone
and three button remote
for music and calls
(SE215_{m+SPE} only)*

- Black
- Clear
- White

Made for



SE 112
SE 112_{m+}

Sound Isolating™ Earphones
Great sound + deep bass



SPEAKER
Dynamic MicroDriver

INCLUDES

- Soft flex sleeves (S, M, L)
- Carrying pouch



*Inline microphone
and three button remote
for music and calls
(SE112_{m+} only)*

- Gray

Made for



SE Sound Isolating™ Earphones

Specifications and Accessories



Model	SE112 SE112m+	SE215 SE215m+SPE	SE315	SE425
SOUND SIGNATURE	Great sound + deep bass	Detailed sound + enhanced bass	Full range sound	Accurate + balanced sound

Specifications

DRIVER	◀ Single	◀ Single	◀ Single High-Definition	◀◀ Dual High-Definition
SENSITIVITY (1 kHz)	105 db SPL/mW	107 db SPL/mW	116 db SPL/mW	109 db SPL/mW
IMPEDANCE (Nominal, 1 kHz)	16 Ω	17 Ω	27 Ω	22 Ω
FREQUENCY RANGE	25 Hz – 17 kHz	22 Hz – 17.5 kHz 21 Hz – 17.5 kHz*	22 Hz – 18.5 kHz	20 Hz – 19 kHz
CABLE	Attached 50" (127 cm) cable Attached 50" (127 cm) cable with Remote + Mic*	Detachable 64" (162 cm) cable with wireform fit Detachable 50" (127 cm) with Remote + Mic and wireform fit*	Detachable 64" (162 cm) cable with wireform fit	Detachable 64" (162 cm) cable with wireform fit
COLORS	Gray	Clear, Black, White*	Clear, Black	Clear, Metallic Silver

*SE112m+ Only

*SE215m+SPE Only

Accessories

SOFT FLEX SLEEVES (S,M,L)				
FOAM SLEEVES (S,M,L)				
YELLOW FOAM SLEEVES				
TRIPLE FLANGE SLEEVES				
ROAD CASE				
PREMIUM CARRYING CASE				
CARRYING CASE/POUCH				
1/4" ADAPTER				
AIRLINE ADAPTER				
VOLUME CONTROL				
NOZZLE REMOVAL KEY				
NOZZLE INSERTS				
POLISHING CLOTH				



SE535


SE846

Spacious sound
+ rich bass

Extended high-end
clarity + unparalleled
low-end performance

Detachable. Replaceable. Customizable.

Shure Sound Isolating™ Earphones feature detachable, Kevlar™ reinforced cables that allow for easy replacement or customization.



Remote + Mic *(sold separately)*

CONVENIENCE AND CONTROL AT YOUR FINGERTIPS

Add the Remote + Mic Accessory cables for an instant hands-free upgrade for Shure earphones with detachable cables. Seamlessly control mobile device functions and media playback with a durable, sleek remote. The Remote + Mic Lightning Accessory delivers digital audio over a standard Lightning™ connection.



RMCE


RMCE-LTG

Isolation, not cancellation.



ISOLATION

Sound isolating earphones naturally block most background noise for a clear, detailed listening experience.



CANCELLATION

Noise cancellation technology uses active circuitry to counteract background noise, which may introduce artifacts into your audio.

◀◀◀ Triple High-Definition	◀◀◀◀ Quad High-Definition
119 db SPL/mW	114 db SPL/mW
36 Ω	9 Ω
18 Hz – 19 kHz	15 Hz – 20 kHz
Detachable 64" (162 cm) cable with wireform fit	Detachable 64" (162 cm) and 46" (116 cm) cables with wireform fit
Clear, Metallic Bronze	Clear, Bronze, Blue, Black

SRH Headphones

Specifications and Accessories

PORTABLE







Model	SRH144	SRH145/m+	SRH240A	SRH440
USE	Designed for detailed listening on the go	Designed for immersive listening on the go	Ideal for vivid listening on almost any device	Developed for professional and home studios

Specifications

DESIGN	Semi-open, Supra-aural	Closed-Back, Supra-aural	Closed-Back, Circumaural	Closed-Back, Circumaural
DRIVER	36 mm dynamic, neodymium magnet	36 mm dynamic, neodymium magnet	40 mm dynamic, neodymium magnet	40 mm dynamic, neodymium magnet
SENSITIVITY (1 kHz)	96 dB/mW	100 dB/mW	107 dB/mW	105 dB/mW
IMPEDANCE (Nominal, 1 kHz)	34 Ω	34 Ω	38 Ω	44 Ω
MAX INPUT POWER (1 kHz)	200 mW	200 mW	500 mW	500 mW
FREQUENCY RANGE	30 Hz – 20 kHz	25 Hz – 18 kHz	20 Hz – 20 kHz	10 Hz – 22 kHz
NET WEIGHT (w/o cable)	.33 lb (150 g)	.33 lb (150 g)	.52 lb (238 g)	.69 lb (311 g)
CABLE TYPE	Straight, dual-side	Straight, dual-side	Straight, attached oxygen-free copper	Coiled, single-exit, detachable oxygen-free copper
CABLE LENGTH	1.52 m (5 ft)	1.52 m (5 ft)	2 m (6.56 ft)	3 m (9.84 ft)
PLUG	Nickel-plated 1/8" (3.5mm) stereo jack	Nickel-plated 1/8" (3.5mm) stereo jack	Gold-plated 1/8" (3.5mm) stereo jack	Gold-plated 1/8" (3.5mm) stereo jack

Accessories

ADDITIONAL PAIR OF EAR PADS				
DETACHABLE CABLE				
THREADED 1/4" ADAPTER			 (Nickel-Plated)	
HARD STORAGE CASE				
CARRYING BAG				

STUDIO



SRH550DJ

SRH750DJ

SRH840

SRH940

Designed for DJ mixing and personal listening

Engineered for live professional DJ mixing and monitoring

Optimized for professional studio recording

Designed for critical listening, monitoring and mastering

Closed-Back, Supra-aural	Closed-Back, Circumaural	Closed-Back, Circumaural	Closed-Back, Circumaural
50 mm dynamic, neodymium magnet	50 mm dynamic, neodymium magnet	40 mm dynamic, neodymium magnet	40 mm dynamic, neodymium magnet
109 dB/mW	106 dB/mW	102 dB/mW	100 dB/mW
32 Ω	40 Ω	44 Ω	42 Ω
3000 mW	3000 mW	1000 mW	1000 mW
5 Hz – 22 kHz	5 Hz – 30 kHz	5 Hz – 25 kHz	5 Hz – 30 kHz
.52 lb (235 g)	.64 lb (291 g)	.82 lb (372 g)	.71 lb (322 g)
Straight, attached oxygen-free copper	Coiled, single-exit, detachable oxygen-free copper	Coiled, single-exit, detachable oxygen-free copper	Single-exit, detachable oxygen-free copper
2 m (6.56 ft)	3 m (9.84 ft)	3 m (9.84 ft)	Coiled: 3 m (9.84 ft) Straight: 2.5 m (8.2 ft)
Gold-plated 1/8" (3.5mm) stereo jack	Gold-plated 1/8" (3.5mm) stereo jack	Gold-plated 1/8" (3.5mm) stereo jack	Gold-plated 1/8" (3.5mm) stereo jack

SRH Headphones

Specifications and Accessories

PREMIUM















Model	SRH1440	SRH1540	SRH1840
USE	Designed for mastering and critical listening	Designed for critical listening and monitoring	Designed for mastering and critical listening

Specifications

DESIGN	Open-Back, Circumaural	Closed-Back, Circumaural	Open-Back, Circumaural
DRIVER	40 mm dynamic, neodymium magnet	40 mm dynamic, neodymium magnet	40 mm dynamic, neodymium magnet
SENSITIVITY (1 kHz)	101 dB/mW	99 dB/mW	96 dB/mW
IMPEDANCE (Nominal, 1 kHz)	37 Ω	46 Ω	65 Ω
MAX INPUT POWER (1 kHz)	1000 mW	1000 mW	1000 mW
FREQUENCY RANGE	15 Hz – 27 kHz	5 Hz – 25 kHz	10 Hz – 30 kHz
NET WEIGHT (w/o cable)	.76 lb (343 g)	.63 lb (286 g)	.59 lb (268 g)
CABLE TYPE	Straight, dual-exit, detachable oxygen-free copper	Straight, dual-exit, detachable oxygen-free copper	Straight, dual-exit, detachable oxygen-free copper
CABLE LENGTH	2.1 m (6.9 ft)	1.8 m (6 ft)	2.1 m (6.9 ft)
PLUG	Gold-plated 1/8" (3.5mm) stereo jack	Gold-plated 1/8" (3.5mm) stereo jack	Gold-plated 1/8" (3.5mm) stereo jack

Accessories

ADDITIONAL PAIR OF EAR PADS			
DETACHABLE CABLE			
THREADED 1/4" ADAPTER			
HARD STORAGE CASE			
CARRYING BAG			

Made for



iPod



iPhone



iPad

"Made for iPod," "Made for iPhone," and "Made for iPad" mean that an electronic accessory has been designed to connect specifically to iPod, iPhone, or iPad, respectively, and has been certified by the developer to meet Apple performance standards. Apple is not responsible for the operation of this device or its compliance with safety and regulatory standards. Please note that the use of this accessory with iPod, iPhone, or iPad may affect wireless performance.

iPad, iPhone, iPod and iPod touch are trademarks of Apple Inc., registered in the U.S. and other countries. iPad Air, iPad mini and Lightning are trademarks of Apple Inc.

Legendary performance.™

From professional applications to everyday personal listening, Shure products deliver an unparalleled combination of precision sound and rugged durability that has made them the choice of musicians and music lovers for over 90 years.



SHURE[®]
LEGENDARY
PERFORMANCE™

**United States, Canada,
Latin America, Caribbean:**
Shure Incorporated
5800 West Touhy Avenue
Niles, IL 60714-4608 USA

Phone: 847-600-2000
Fax: 847-600-1212 (USA)
Fax: 847-600-6446
Email: info@shure.com

Europe, Middle East, Africa:
Shure Europe GmbH
Jakob-Dieffenbacher-Str. 12,
75031 Eppingen, Germany

Phone: 49-7262-92490
Fax: 49-7262-9249114
Email: info@shure.de

Asia, Pacific:
Shure Asia Limited
22/F, 625 King's Road
North Point, Island East
Hong Kong

Phone: 852-2893-4290
Fax: 852-2893-4055
Email: info@shure.com.hk