


Part Number: SY-Stealth-18G

Applications:

Connect 4K sources and display for the best image and HDR effect. Discrete connection for racks.

Ideal use:

High end 4K home AV systems. An Ideal cable for rack connections.




Available in the following lengths:
0.3m, 0.5m, 0.75m, 1.0m, 1.5m, 2.0m

The SY Stealth 18G

- The slimmest 18Gbps HDMI cable available**
 Only 3.45mm in diameter. Pliable construction making it the easiest 18Gbps link to conceal.
- 18Gbps. Faster. Superior bandwidth**
 The highest bandwidth for the best 4K. Enjoy superior colour with uncompromised HDR performance.
- Metal plugs**
 Preventing emission of RF and interference of WiFi transmission. I
- Connect and forget**
 Ensure connection integrity. Secured firm fixing.
- Compact. Light. Easy to conceal**
 Starting at 15 grams this unique range can easily be positioned in any conceivable environment.
- Striking design**
 The Stealth 18G is combining technology with a striking aesthetic statement

SY Stealth 18G Link
The Slimmest HDMI 2.0v available
Stealth 18G



- Max. Resolution 3840x2160
- Support for 4190x2160
- ARC
- Ethernet
- HDMI 2.0v
- HDCP2.2
- RGB to 16Bits colour depth.
- REC.2020
- 24 to 60Hz refresh rate.
- 4:2:0/4:2:2/4:4:4 Sub Sampling.
- 1536Hz max audio frequency.
- 192/24 max audio resolution.
- Simultaneous dual video stream
- HDR
- Dolby Vision
- HLG

Available lengths:
0.3, 0.5, 0.75, 1.0, 1.5, 2.0m



- 18Gbps
- HDR 1.07 Billion colours
- ARC channel
- Ethernet

4K60 4:4:4 18Gbps ARC Ethernet HDR

Slimmer. Faster. Lighter.
Ideal for multi connection settings on racks.
Metal construction and isolation from end to end.
Best HDR performance.
ARC and Ethernet.

SPECIFICATIONS

VIDEO RESOLUTIONS

VESA and SMPTE 480p to 2160p (4K/UHD/4K2K) with 3D. (All resolutions to: Supports 3840x2160p @24 to 60Hz 4:2:0 to 4:4:4 Colour depth of 8/10/12/16bit. REC.2020 Supports 4096x2160, supports 21:9 aspect ratio)

BANDWIDTH

18Gbps

HDCP

Compatible with all version up to 2.2v

FEATURES

ARC, Ethernet, Up to 32 audio channels, up to 1536kHz audio sample frequency, up to 192/24 audio resolution,

Simultaneous dual video streams, simultaneous audio streams, support for 21:9 aspect ratio, extended CEC protocol, Support HDR, Dolby vision, HLG

CONNECTOR

Die cast HDMI type A 2.0v

SLEEVE

PVC

Sleeve's diameters

3.40mm

LENGTH

0.3/0.5/0.75/1.0/1.5/2.0m

WEIGHT

0.3 -13g

0.5 -18g

0.75 -21g

1.0 -26g

1.5 -34g

1.5 -41g



Developer member HDBaseT alliance

"HDMI, the HDMI Logo, and High-Definition Multimedia Interface are trademarks or registered trademarks of the HDMI Licensing LLC in the United States and other countries"

Details subject to change with no prior notice

©SY electronics 2018

+44(0)161 868 3450 www.sy.uk