

BA9LED4P

Specifications and dimensions



- Bayonet fix LED lamp
- Low maintenance due to long life and high reliability
- Last 500 times as long as incandescent lamps

Features	
Colour	Red
Voltage	230V AC/DC
Other colours available	White, Green, Amber, Blue
Other voltages available	24V AC/DC, 110V AC/DC
Diameter	10mm
Overall length	23mm
Number of chips	2
Wavelength green (gallium phosphide)	5600Å
Wavelength yellow (gallium arsenide phosphide)	5800Å
Wavelength amber (gallium arsenide phosphide)	6300Å
Wavelength red (gallium arsenide phosphide)	6600Å
Degree of protection	IP55
Operating temperature	-25°C to +55°C
Life expectancy	30000 hours

ⓘ ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Information provided in data sheets and/or specifications may vary from actual results in different applications and performance may vary over time. **All products must be installed according to manufacturers instructions.**

Europa House, Airport Way, Luton, Beds, LU2 9NH Tel: 01582 692 440 / Fax: 01582 692 450 e-mail: sales@europacomponents.com
website: <http://www.europacomponents.com>