




D-Sub Backshells DPPK-Series

TECHNICAL SPECIFICATIONS

Material:	Nylon UL94 V2
Temp. range:	-55°C - 105°C
Cable strain relief:	Cable clamp with self-tapping screws
Cable diameter:	3.0 - 11.0 mm
Locking screws:	Long jackscrews with moulded top for colour coding
Cable outlet:	Straight



TYPE	A	B
DPPK9	32,4	31,3
DPPK15	40,7	30,8
DPPK25	54,4	37,3
DPPK37	70,9	36

PART NUMBERING SYSTEM

DPPK25 - M2.6 - RED - K

Series: _____
 DPPK
 Size: _____
 9, 15, 25 or 37
 Thread (jackscrew): _____
 Omit = UNC 4-40
 M2.5
 M2.6
 M3.0

Packaging:
 K = Kit package
 BULK = Bulk package / 100 pcs
 Colour:
 Omit = Black
 Other colours available: beige, blue, brown, green, grey, ivory, red, white and yellow

FEATURES

- Available in sizes 9, 15, 25 and 37
- Hinged single piece moulding with retaining latches
- Light weight and cost effective
- Compact and attractive design
- Company logotype available upon request
- Long jackscrews with UNC 4-40 thread as standard, M2.5, M2.6 or M3.0 as option
- For custom designed solutions, please consult factory

