



WIRELESS 2000

ANNUNCIATOR SYSTEM

RCTD-20U WIRELESS SYSTEM

Wireless Driveway
& Entry Announcer



BE AWARE, BE SECURE.

The Wireless 2000 from OPTEX is a wireless annunciator system that not only alerts businesses to customers entering their store, but also can provide driveway/entry annunciation and perimeter awareness to residential customers. Whether for home or business, indoor or out, the Wireless 2000 system is the ideal choice for entry alerts and visitor awareness with wireless remote control.

Expandability matched by no other wireless alert system on the market.



BE AWARE, BE SECURE.



TD-20U




RC-20U

NO MORE SURPRISES

The OPTEX Wireless 2000 monitors your property 24 hours a day to detect approaching vehicles and people, giving you time to prepare.

NO MORE MISSED VISITORS OR DELIVERIES


The OPTEX Wireless 2000 serves as a welcome chime or perimeter alert for your home or business.



The Wireless 2000 includes an outdoor rated wireless PIR detector, as well as an R.F. receiver that can hold up to 9 detectors and chimes when the sensor detects motion. The R.F. receiver also features a Form C relay for activation of doors, locks, gates, cameras, and other electronic equipment.


Additional accessories can be added, including the TC-20U wireless door/window contact, TS-10U wireless push button transmitter for notification or activation applications, and TR-20U repeater for applications where extended range for Wireless 2000 devices is necessary.

EASILY EXPANDABLE



The RDTD-20U offers expandability matched by no other wireless alert system on the market. With four channels and three unique chime tones, users can add up to nine TD-20U sensors to one RC-20U chime box receiver. The fourth channel on the chime box can accept three more transmitters and acts as a latching alarm, and will continue to chime until the user turns it off. In addition, up to five RC-20U receivers can be used per system.

The selectable 17ft. fan pattern or 50ft. beam pattern on the battery-operated TD-20U make it a versatile option for perimeter awareness



TRANSMISSION RANGE

TD-20U.....	2,000ft
TS-10U.....	700ft
TC-10U.....	700ft
TR-20U (TD-20U to Repeater).....	1,000ft
TR-20U (TC & TS-10U to Repeater)...	700ft
TR-20U (Repeater to Receiver).....	1,000ft

These measurements were obtained with receivers & transmitters mounted 7ft. above level ground without obstructions. Natural & man-made obstructions and other environmental factors do shorten transmission ranges.

ADDITIONAL ACCESSORIES



TR-20U

Hardwired Repeater

The TR-20U is a hardwired repeater for the RCTD-20U (Wireless 2000). It extends the range between either the TD-20U, TC-20U or TS-10U, and the RC-20U receiver of up to 1,000 additional feet (depending on device, line of sight).



TS-10U

Push Button Wireless Transmitter

The TS-10U is a push button, battery-powered transmitter for the RCTD-20U (Wireless 2000). It allows the user to send a signal back to the RC-20U chime box and creates a chime for notification purposes, as well as triggering or releasing other devices such as magnetic door locks and lighting.



TC-10U

Wireless Door Contact/Transmitter



The TC-10U is a battery-powered door/window contact and wireless transmitter for the RCTD-20U (Wireless 2000). When used as a wireless transmitter and installed in the back-box of any of OPTEX's battery operated detectors, extended detection range and wireless notification to your RC-20U chime box is achieved. Instantly monitor larger areas with minimal false alarms for a greater sense of protection. When used as a door contact, the TC-10U will send a signal to the RC-20U receiver chime box. This gives the user a notification when the door is opened, and is perfect for high traffic areas around entrances where an above door sensor is not practical.



WIRELESS 2000

ANNUNCIATOR SYSTEM

SPECIFICATIONS

MODEL	RC-20U	TD-20U	TR-20U	TS-10U	TC-10U
Description	Chime Box w/Relay	In/Outdoor Sensor transmitter	Repeater	Hand-Held transmitter	DoorContact/Wireless transmitter
Detection method	--	Passive infrared	--	Push button	Built in magnet
Detection pattern	--	50ft (15m) long range 17ft (5m) fan pattern	--	--	--
Angle adjustment	--	90° vert. & ±5° horizontally or ±5° vert. & 90° horizontally	--	--	--
Power source	DC 9V (exclusive AD adapter)	9V battery, not included	DC 9V (exclusive AC adapter)	AA batteries x2, not included	CR123 3V battery, not included
Power consumption	Standby: 1W, Operating: 2W	--	Standby: 1W, Operating: 2W	--	--
Battery life	--	Approx. 2 yrs [250/day at 70°F (20°C)]	--	Approx. 2yrs [100/day at 70°F (20°C)]	Approx. 2yrs [100/day at 70°F (20°C)]
Chime tone	3 tone & 1 alarm (optional)	--	--	--	--
Volume	Adjustable: 0~80dB/5 levels (Continuous zone: max.)	--	--	--	--
Relay output	50V AC 1A max or 24V DC 1A max.	--	--	--	--
Output timer	Selectable: off/1/5/30/60sec/ utility output mode	--	--	--	--
Status indicator	Power indicator: green LED Zone indicator: red LED x 3	Red LED	Power indicator: green LED Zone indicator: red LED x 3	Red LED	Red LED
Radio frequency	418MHz	418MHz	418MHz	418MHz	418MHz
Max. trans range	--	2000ft (line of sight)	1000ft	700ft (line of sight)	700ft (line of sight)
Operating temp.	15°F to 104°F (-10°C to +40°C)	15°F to 120°F (-10°C to +50°C)	15°F to 120°F (-10°C to +50°C)	15°F to 120°F (-10°C to +50°C)	15°F to 120°F (-10°C to +50°C)
Water resistance	--	IP54	--	--	--
Installation location	Indoor	Outdoor/Indoor	Indoor	Indoor	Indoor/Outdoor
Weight	6.0oz (170g)	6.3oz (180g)	6.0oz (170g)	1.4oz (40g)	2.5oz (70g)
Accessories	AC adapter x 1 Mounting screw x1	Mounting screw x 2	AC adapter x 1 Mounting screw x 1	Belt clip x 1	Double stick tape x 3 Screw x 4, Washer x 2

Note: Specifications may change without notice. RC-20, TR-20, TD-20, and TS-10 are not theft prevention units. OPTEX can not assume responsibility for a theft, should it occur. All products listed come with 2-year warranty.

