



Quality Products. Service Excellence.

## Economy Fixed Wall Mount Cabinet *RB-FW Series*

130 lbs Weight Capacity

### Features



- Constructed in light duty 16-gauge steel.
- Includes two (2) pairs of EIA-310-D compliant 19 inch square hole mounting rails.
  - Starter pack of (25) M6 screws, cage nuts and washers included.
  - For 10-32 hardware see the **CAGKIT Series**.
- Rails are adjustable.
- Includes one (1) locking tempered glass lightly smoked reversible front door.
- Includes one (1) pair of locking removable side panels.
- Front and side of frame includes venting for air flow.
- Rear cable access.
- Provision for optional fans on top panel.
- Ships un-assembled - some assembly required.
- Finished in black powder paint.
- Tested to 130 lbs (59 kg) of equipment load capacity.
- RoHS Compliant.

Part of the Rack Basics® line of economy rack solutions.

**RACK BASICS®**



### Accessories

- Horizontal Ring Cable Manager
- Horizontal Lacing Strip
- Outlet Strips
- Mounting Hardware
- Universal Rack Shelf
- Cable Lacing Bar
- Fan Kits



| Part No. | Overall Dimensions |       |       | Rack Units | Mounting Dimensions |       |       | Usable Depth |
|----------|--------------------|-------|-------|------------|---------------------|-------|-------|--------------|
|          | Height             | Width | Depth |            | Height              | Width | Depth |              |
| RB-FW6   | 14.65              | 23.62 | 23.62 | 6U         | 10.50               | 19.00 | 16.93 | 21.24        |
| RB-FW9   | 19.90              | 23.62 | 23.62 | 9U         | 15.75               | 19.00 | 16.93 | 21.24        |
| RB-FW12  | 25.15              | 23.62 | 23.62 | 12U        | 21.00               | 19.00 | 16.93 | 21.24        |
| RB-FW15  | 30.40              | 23.62 | 23.62 | 15U        | 26.25               | 19.00 | 16.93 | 21.24        |

Note: Usable depth is the furthest depth equipment can be mounted in the cabinet.

Data subject to change without notice

© 2018. Hammond Manufacturing Ltd. All rights reserved.

