



## NT 40/1 TACT TE L \*GB 240V

The NT 40/1 Tact Te L is designed for the pickup of very large quantities of hazardous dusts, suitable for dust class L. It is robust yet highly mobile, featuring a 40 litre container.





**NT 40/1 TACT TE L \*GB 240V**

■ Anti-static preparation

## Technical data

<b>Order Number</b>	1.148-314.0	
<b>EAN code</b>	4054278299938	
<b>Air flow</b>	<b>l/s</b>	74
<b>Vacuum</b>	<b>mbar / kPa</b>	254 / 25,4
<b>Container capacity</b>	<b>l</b>	40
<b>Max. rated input power</b>	<b>W</b>	1380
<b>Standard nominal size</b>		35
<b>Sound level</b>	<b>dB(A)</b>	69
<b>Container material</b>		Plastic
<b>Quantity of motors</b>		1
<b>Frequency</b>	<b>Hz</b>	50-60
<b>Voltage</b>	<b>V</b>	220-240
<b>Weight</b>	<b>kg</b>	14,4
<b>Dimensions (L x W x H)</b>	<b>mm</b>	560 × 370 × 655

## Equipment

<b>Suction hose</b>	<b>m</b>	4	<b>Caster with brake</b>	■
<b>Filter bag</b>		Fleece	<b>Filter cleaning</b>	Tact Filter Clean
<b>Wet and dry floor tool</b>	<b>mm</b>	360 / standard		■
<b>Crevice nozzle</b>		■		
<b>Connector for electric tools</b>		■		
<b>Auto shutdown when max. level is reached</b>		■		
<b>Automatic on/off control for electric power tools</b>		■		
<b>Antistatic system</b>		■		
<b>Flat pleated filter</b>		PES		
<b>Sturdy bumper</b>		■		
<b>Safety class</b>		I		

■ Included in delivery.

# ACCESSORIES FOR NT 40/1 TACT TE L \*GB 240V

## 1.148-314.0

**KÄRCHER**



		Order Number	Quantity	ID	Length	Width	Price	Description		
<b>Flat pleated filter (PES)</b>										
Flat pleated filter (PES)	1	6.904-360.0	1 piece(s)					Flat pleated filter (PES) - BIA-C dust class M: rotproof polyester fleece, ideal for wet use and abrasives. Standard for NT 35/1 Eco BS and NT 55/1 Eco BS.	<input checked="" type="checkbox"/>	
<b>Fleece filter bags (3 ply)</b>										
Filter bags-fleece 5 piece 40-50 Liter	2	2.889-155.0	5 piece(s)						<input checked="" type="checkbox"/>	
<b>Plastic bend</b>										
Elbow packaged NW35 2K	3	2.889-170.0	1 piece(s)	ID 35					<input checked="" type="checkbox"/>	
Elbow electrically conducting packaged N	4	2.889-148.0	1 piece(s)	ID 35					<input type="checkbox"/>	
Elbow complete packaged NW35 2K	5	2.889-168.0	1 piece(s)	ID 35					<input type="checkbox"/>	
<b>All-purpose nozzles (wet/dry)</b>										
Floor tool packaged NW35 360mm	6	2.889-152.0	1 piece(s)	ID 35		360 mm			<input checked="" type="checkbox"/>	
Floor tool DN35	7	6.906-512.0	1 piece(s)	ID 35		300 mm		All-purpose plastic nozzle (DN 35) with 300 mm working width. With side rollers, brush strips (6.903-278.0) and squeegees (6.903-277.0). Only for NT vacuum cleaners.	<input type="checkbox"/>	
Floor tool neutrally DN35	8	6.906-384.0	1 piece(s)	ID 35		370 mm		All-purpose aluminium nozzle (DN 35) with 370 mm working width. With height-adjustable side rollers, brush strips (6.903-064.0) and oil-resistant squeegees (6.903-081.0). Only for NT vacuum cleaners.	<input type="checkbox"/>	
	9	2.889-118.0	1 piece(s)	ID 35		400 mm			<input type="checkbox"/>	
<b>Crevice nozzles</b>										
Crevice nozzle wet and dry packaged NW35	10	2.889-159.0	1 piece(s)	ID 35	225 mm				<input checked="" type="checkbox"/>	
<b>Suction tubes stainless steel</b>										
Set suction tube stainless steel NW35 55	11	2.889-192.0	1 piece(s)	ID 35	550 mm				<input checked="" type="checkbox"/>	
<b>Suction hoses complete (Clip-system)</b>										
Hose packaged NW35 2.5m	12	2.889-134.0	1 piece(s)	ID 35	2,5 m				<input type="checkbox"/>	
Hose electrically conducting packaged NW	13	2.889-136.0	1 piece(s)	ID 35	2,5 m				<input type="checkbox"/>	
	14	2.889-137.0	1 piece(s)	ID 35	4 m				<input type="checkbox"/>	
<b>Adapter for electric power tools, clip on, el.</b>										
Sleeve electrically conducting packaged	15	2.889-151.0	1 piece(s)	ID 35					<input checked="" type="checkbox"/>	
<b>Flat pleated filter (paper)</b>										
Flat filter only for replacement Kaerche	16	6.904-367.0	1 piece(s)					Paper flat pleated filter (dust class M) suitable for NT 361, NT 561, NT 611 Eco/Te/M and NT 35/1, NT 45/1, NT 55/1 Eco/Eco Te/Eco M.	<input type="checkbox"/>	
<b>Flachfaltenfilter (PTFE)</b>										
	17	6.907-455.0	1 piece(s)						<input type="checkbox"/>	
<b>Coarse filter for wet pickup</b>										
Coarse dirt filter for wet pick up	18	6.904-287.0	1 piece(s)					Coarse dirt filter with perforated metal plate and foam seal suitable for wet pick up - NT 611 Eco K & KF models.	<input type="checkbox"/>	
<b>HEPA filter for dust class H</b>										
HEPA surface filter	19	6.904-242.0	1 piece(s)					HEPA surface filter - dust class H (HEPA 13) - with glass-fibre layers increases filter capacity when vacuuming health-endangering and carcinogenic dust.	<input type="checkbox"/>	
<b>Plastic sacks for dust-free disposal</b>										
Disposal bag 10-parts PE	20	2.889-158.0	10 piece(s)						<input type="checkbox"/>	

■ Included in delivery. □ Available accessories.

# ACCESSORIES FOR NT 40/1 TACT TE L \*GB 240V

## 1.148-314.0

**KÄRCHER**



		Order Number	Quantity	ID	Length	Width	Price	Description	
<b>All-purpose brushes</b>									
All-purpose brush	21	6.900-425.0	1 piece(s)	ID 35	120 mm			All-purpose brush PPN_Bristle	<input type="checkbox"/>
<b>Car cleaning nozzles</b>									
Car nozzle DN35	22	6.906-108.0	1 piece(s)	ID 35		90 mm		Angled, flat, plastic car vacuuming tool with about 90 mm working width. Only for NT vacuum cleaners.	<input type="checkbox"/>
<b>Combi-nozzles (dry)</b>									
Combination floor tool (dry)	23	6.906-511.0	1 piece(s)	ID 35		270 mm		Combination floor tool with changeover function, plastic (272 mm). With stainless steel base plate, thread catcher 6.905-417.0 and DN 35 connection.	<input type="checkbox"/>
<b>Suction brushes</b>									
Suction brush DN35	24	6.903-862.0	1 piece(s)	ID 35		70 mm		Rotatable suction brush (DN 35) with natural bristles (cow hair). Bristle size 70x45 mm. Only CV and NT vacuum cleaners.	<input type="checkbox"/>
<b>Other</b>									
Drilling dust tool	25	2.679-000.0	1 piece(s)						<input type="checkbox"/>
<b>Adapter for electric power tools, screwable</b>									
Power tool adapter, threaded, DN 35	26	5.453-016.0	1 piece(s)	ID 35				3-way plastic adapter with fitting instructions. For DN 26 to DN 36. For connecting to an industrial DN 35 suction hose.	<input type="checkbox"/>
<b>Target group specific vacuum cleaner accessory sets</b>									
Universal kit for industrial and commercial use	27	2.637-595.0		ID 35				Accessory kit for industrial and commercial use.	<input type="checkbox"/>
Boiler cleaning kit	28	2.638-852.0		ID 35				Accessory kit for vacuuming and cleaning boilers, oil stoves, etc.	<input type="checkbox"/>
Car cleaning kit	29	2.862-166.0		ID 35				Contains: - Car cleaning nozzle ID 35 - Upholstery/crevice tool ID 35 - Suction brush ID 35 - Connecting sleeve C 35/ ID 35	<input type="checkbox"/>

■ Included in delivery. □ Available accessories.