



NT 40/1 TACT TE M *GB 240V

The NT 40/1 Tact Te M is designed for the pickup of very large quantities of hazardous dusts, suitable for dust class M. It is robust yet highly mobile, featuring a 40 litre container.



NT 40/1 TACT TE M *GB 240V

Technical data

Order Number	1.148-355.0	
EAN code	4054278483696	
Air flow	l/s	74
Vacuum	mbar / kPa	237 / 23,7
Container capacity	l	40
Max. rated input power	W	1380
Standard nominal size	35	
Sound level	dB(A)	68
Weight	kg	15,1
Dimensions (L x W x H)	mm	560 × 370 × 655

Equipment

Suction hose	m	4	Caster with brake	■
Filter bag	Fleece		Filter cleaning	Tact Filter Clean
Wet and dry floor tool	mm	360	Dust class	M
Crevice nozzle	■			
Connector for electric tools	■			
Automatic on/off control for electric power tools	■			
Antistatic system	■			
Eco filter system	■			
Flat pleated filter	PES			
Sturdy bumper	■			
Safety class	I			

■ Included in delivery.

ACCESSORIES FOR NT 40/1 TACT TE M *GB 240V 1.148-355.0

KÄRCHER



		Order Number	Quantity	ID	Length	Width	Price	Description	
Fleece filter bags (3 ply)									
Filter bags-fleece 5 piece 40-50 Liter	1	2.889-155.0	5 piece(s)						■
Plastic bend									
Elbow complete packaged NW35 2K	2	2.889-168.0	1 piece(s)	ID 35					■
All-purpose nozzles (wet/dry)									
Floor tool packaged NW35 360mm	3	2.889-152.0	1 piece(s)	ID 35		360 mm			■
Crevice nozzles									
Crevice nozzle wet and dry packaged NW35	4	2.889-159.0	1 piece(s)	ID 35	225 mm				■
Suction tubes stainless steel									
Set suction tube stainless steel NW35 55	5	2.889-192.0	1 piece(s)	ID 35	550 mm				■
Suction hoses complete (Clip-system)									
Hose electrically conducting packaged NW	6	2.889-137.0	1 piece(s)	ID 35	4 m				■
Adapter for electric power tools, clip on, el.									
Sleeve electrically conducting packaged	7	2.889-151.0	1 piece(s)	ID 35					■
Car cleaning nozzles									
Car nozzle DN35	8	6.906-108.0	1 piece(s)	ID 35		90 mm		Angled, flat, plastic car vacuuming tool with about 90 mm working width. Only for NT vacuum cleaners.	□

■ Included in delivery. □ Available accessories.