



## **NT 30/1 TACT TE H \*GB 110v**

With a guaranteed filtration efficiency of 99.995%, the 30/1 Tact Te H wet and dry vacuum cleaner is the first choice for removing dusts hazardous to health in dust class H. Available with 110v supply.



## NT 30/1 TACT TE H \*GB 110v

### Technical data

<b>Order Number</b>	1.148-249.0	
<b>EAN code</b>	4054278483689	
<b>Air flow</b>	<b>l/s</b>	71
<b>Vacuum</b>	<b>mbar / kPa</b>	190 / 19
<b>Container capacity</b>	<b>l</b>	30
<b>Max. rated input power</b>	<b>W</b>	1100
<b>Standard nominal size</b>		35
<b>Sound level</b>	<b>dB(A)</b>	69
<b>Weight</b>	<b>kg</b>	15
<b>Dimensions (L x W x H)</b>	<b>mm</b>	560 × 370 × 580


### Equipment

<b>Suction hose</b>	<b>m</b>	4	<b>Caster with brake</b>	■
<b>Filter bag</b>		Fleece	<b>Filter cleaning</b>	Tact Filter Clean
<b>Wet and dry floor tool</b>	<b>mm</b>	360		
<b>Crevice nozzle</b>		■		
<b>Connector for electric tools</b>		■		
<b>Automatic on/off control for electric power tools</b>		■		
<b>Antistatic system</b>		■		
<b>Eco filter system</b>		■		
<b>Flat pleated filter</b>		Fibreglass		
<b>Sturdy bumper</b>		■		
<b>Safety class</b>		I		

■ Included in delivery.

# ACCESSORIES FOR NT 30/1 TACT TE H \*GB 110V 1.148-249.0

**KÄRCHER**



		Order Number	Quantity	ID	Length	Width	Price	Description	
<b>Plastic bend</b>									
Elbow complete packaged NW35 2K	1	2.889-168.0	1 piece(s)	ID 35					<input checked="" type="checkbox"/>
Elbow packaged NW35 2K	2	2.889-170.0	1 piece(s)	ID 35					<input type="checkbox"/>
<b>All-purpose nozzles (wet/dry)</b>									
Floor tool packaged NW35 360mm	3	2.889-152.0	1 piece(s)	ID 35		360 mm			<input checked="" type="checkbox"/>
<b>Crevice nozzles</b>									
Crevice nozzle wet and dry packaged NW35	4	2.889-159.0	1 piece(s)	ID 35	225 mm				<input checked="" type="checkbox"/>
<b>Suction tubes stainless steel</b>									
Set suction tube stainless steel NW35 55	5	2.889-192.0	1 piece(s)	ID 35	550 mm				<input checked="" type="checkbox"/>
Set suction tube stainless steel NW40 55	6	2.889-194.0	1 piece(s)	ID 40	550 mm				<input type="checkbox"/>
Suction tube, ID 40	7	6.902-081.0	1 piece(s)	ID 40	0,5 m			Stainless steel suction tube (DN 40, 0.5 m) only suitable for NT vacuum cleaners.	<input type="checkbox"/>
<b>Suction hoses complete (Clip-system)</b>									
Hose electrically conducting packaged NW	8	2.889-137.0	1 piece(s)	ID 35	4 m				<input checked="" type="checkbox"/>
	9	2.889-136.0	1 piece(s)	ID 35	2,5 m				<input type="checkbox"/>
	10	2.889-161.0	1 piece(s)	ID 35	2 m				<input type="checkbox"/>
<b>Adapter for electric power tools, clip on, el.</b>									
Sleeve electrically conducting packaged	11	2.889-151.0	1 piece(s)	ID 35					<input checked="" type="checkbox"/>
<b>HEPA filter for dust class H</b>									
HEPA surface filter	12	6.904-242.0	1 piece(s)					HEPA surface filter - dust class H (HEPA 13) - with glass-fibre layers increases filter capacity when vacuuming health-endangering and carcinogenic dust.	<input type="checkbox"/>
<b>Plastic sacks for dust-free disposal</b>									
Disposal bag 10-parts PE	13	2.889-158.0	10 piece(s)						<input type="checkbox"/>
<b>Car cleaning nozzles</b>									
Car nozzle DN35	14	6.906-108.0	1 piece(s)	ID 35		90 mm		Angled, flat, plastic car vacuuming tool with about 90 mm working width. Only for NT vacuum cleaners.	<input type="checkbox"/>
<b>Other</b>									
Drilling dust tool	15	2.679-000.0	1 piece(s)						<input type="checkbox"/>

■ Included in delivery. □ Available accessories.