



NT 22/1 AP TE *GB 240V

The NT 22/1 Ap is the new Professional entry class of wet and dry vacuum cleaners. It offers professional quality and provides the ideal cleaning solution to tradesmen.



1 Semi-automatic filter cleaning system



NT 22/1 AP TE *GB 240V

Technical data

Order Number	1.378-612.0	
EAN code	4054278290522	
Air flow	l/s	71
Vacuum	mbar / kPa	255 / 25,5
Container capacity	l	22
Max. rated input power	W	1350
Standard nominal size	35	
Cable length	m	6
Container material	Plastic	
Quantity of motors	1	
Frequency	Hz	50-60
Voltage	V	220-240
Weight	kg	6,1
Dimensions (L x W x H)	mm	380 x 372 x 503

Equipment

Suction hose	m	1,9
Metal suction tube, 2 x 0.5 m	■	
Filter bag	Fleece	
Wet and dry floor tool	mm	300
Crevice nozzle	■	
Connector for electric tools	■	
Automatic on/off control for electric power tools	■	
Cartridge filter	PES	
Safety class	I	
Caster with brake	■	
Filter cleaning	ApClean (semi-automatic filter cleaning system)	

■ Included in delivery.

ACCESSORIES FOR NT 22/1 AP TE *GB 240V 1.378-612.0

KÄRCHER



		Order Number	Quantity	ID	Length	Width	Price	Description	
Cartridge filter PES									
Cartridge filter packaged PES	1	2.889-219.0	1 piece(s)						<input checked="" type="checkbox"/>
Fleece filter bags (3 ply)									
Filter bags fleece 5ST	2	2.889-217.0	5 piece(s)						<input checked="" type="checkbox"/>
Plastic bend									
Elbow packaged NW35 1K	3	2.889-199.0	1 piece(s)	ID 35					<input checked="" type="checkbox"/>
Elbow complete packaged NW35 2K	4	2.889-168.0	1 piece(s)	ID 35					<input type="checkbox"/>
Elbow packaged NW35 2K	5	2.889-170.0	1 piece(s)	ID 35					<input type="checkbox"/>
All-purpose nozzles (wet/dry)									
Floor tool packaged grey DN 35 300mm	6	2.889-263.0	1 piece(s)	ID 35		300 mm			<input checked="" type="checkbox"/>
Floor tool packaged NW35 360mm	7	2.889-152.0	1 piece(s)	ID 35		360 mm			<input type="checkbox"/>
Suction tubes metal									
Suction tube chromed NW35 - 505mm	8	6.902-074.0	1 piece(s)	ID 35	505 mm				<input checked="" type="checkbox"/>
Adapter for electric power tools, screwable									
Attachment rubber sleeve	9	5.303-877.0	1 piece(s)	ID 35					<input checked="" type="checkbox"/>
Car cleaning nozzles									
Car nozzle DN35	10	6.906-108.0	1 piece(s)	ID 35		90 mm		Angled, flat, plastic car vacuuming tool with about 90 mm working width. Only for NT vacuum cleaners.	<input type="checkbox"/>
Crevice nozzles									
Crevice nozzle wet and dry packaged NW35	11	2.889-159.0	1 piece(s)	ID 35	225 mm				<input type="checkbox"/>
Suction tubes stainless steel									
Suction tube stainless steel two parts N	12	2.889-175.0	1 piece(s)	ID 35	505 mm				<input type="checkbox"/>
Suction tubes plastic									
Set suction tube DN35 505mm	13	2.889-218.0	1 piece(s)	ID 35	505 mm				<input type="checkbox"/>
Suction hoses complete (Clip-system)									
Hose packaged NW35 2.5m	14	2.889-134.0	1 piece(s)	ID 35	2,5 m				<input type="checkbox"/>
Hose electrically conducting packaged NW	15	2.889-136.0	1 piece(s)	ID 35	2,5 m				<input type="checkbox"/>
Other									
Drilling dust tool	16	2.679-000.0	1 piece(s)						<input type="checkbox"/>
Adapter for electric power tools, clip on, el.									
Sleeve electrically conducting packaged	17	2.889-151.0	1 piece(s)	ID 35					<input type="checkbox"/>

■ Included in delivery. □ Available accessories.