

10mm Right Angle Keyless Chuck

Code	RADA10
Chuck Capacity	1.5mm to 10mm
Input Drive	9.5mm Round Shaft
Side Handle	Yes - 2 Position
Pack Qty	1
Packaging	Plastic Blister and Insert Card
Weight	482g
Barcode	5039197102889



Description

Lightweight, Rust Free Body
Keyless Operation
Supplied with 2 Position Side Handle
9.5mm Round Drive Shaft
Max Speed 500RPM

Applications

For Drilling in Tight Corners and at Awkward Angles

Suitable For

For use with all makes of mains powered and cordless drills with 10mm chuck capacity or greater
For rotary / percussion drilling only (Not suitable for hammer action drilling)