

# DAC102

## Digital to Analog audio converter

The CE labs digital to analog audio converter allows you to use the best possible signals to drive your analog component. It is small and compact. Plus, there are no adjustments needed for an extra-easy installation.

### KEY FEATURES

- Inputs: 1 Toslink Optical Audio
- 1 Coaxial Audio
- Outputs: 1 R/L Analog Audio
- Support: 32, 44.1, 48 and 96 KHz
- Dimension: 2 x 1.61 x 1.02 (in)



### SPECIFICATIONS

Signal inputs / output	Coaxial or Toslink digital audio
Output audio	L / R audio
Input audio connector	Toslink, 1 X RCA (Coaxial)
Output audio connector	2 x RCA (Coaxial) 1 x .13in
Sampling rate	32, 44.1, 48 and 96 KHz
Size	2X 1.61X 1.02 (in) ; Weight: 78g
Limited warranty	1 year parts and labor
Operating temperature	0°C~+70°C; Storage temperature: -10°C~+80°C; Operating humidity: 10% to 85%RH (no condensation); Storage humidity: 5% to 90% RH (no condensation)
External power supply	DC 5V 2A
Power consumption	0.5watts (max)
Including	Digital to analog audio converter x 1; US plug power adapter x 1; User manure x 1