


## M8-PCB-THT-2PC-4P-DCOD-F-ANG-SHLD



Part number	21 42 010 0003 401
Specification	M8-PCB-THT-2PC-4P-DCOD-F-ANG-SHLD
HARTING eCatalogue	<a href="https://b2b.harting.com/21420100003401">https://b2b.harting.com/21420100003401</a>

### Identification

Category	Connector
Series	Circular connectors M8
Element	PCB connector
Specification	Angled

### Version

Termination method	Wave soldering termination
Gender	Female
Shielding	Shielded
Number of contacts	4
Coding	D-coding
Pack contents	Packaging unit: 25 pieces

### Technical characteristics

Rated current	4 A
Rated voltage	60 V
Rated impulse voltage	1.5 kV
Pollution degree	3
Contact resistance	≤10 mΩ
Ambient temperature	-30 ... +80 °C
Degree of protection acc. to IEC 60529	IP65 IP67
Transmission characteristics	Cat. 5 Class D up to 100 MHz

### Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Au over Ni



Pushing Performance

## Specifications and approvals

Specifications	IEC 61076-2-114
----------------	-----------------

## Commercial data

Packaging size	25
Net weight	4 g
Country of origin	Germany
European customs tariff number	85366990