



Ready when you are

# M Floor to Ceiling Mount Pro MBFC1U

Article: 7 350 073 733 620

M Floor to Ceiling Mount Pro MBFC1U - Ceiling mount for LCD display, steel, 3m length, 1 screen, single side, tilt arms, VESA Max 600x400 - screen size: 40"-65" - black

Product category: PRO SERIES



## Specification

### M Ceiling Mount Pro MBFC1U

<b>Article No:</b>	7 350 073 733 620
<b>For screen size:</b>	40"-65"
<b>Type:</b>	Single Side MBFC1U
<b>Universal &amp; VESA standard:</b>	Adjustable from 100x100 to 600x400 max Optional VESA 800x600
<b>Material:</b>	Steel, Aluminium
<b>Color:</b>	Black
<b>Surface Finish:</b>	Powder coating/Anodic Oxidation
<b>Weight:</b>	13 kg
<b>Measurements</b>	69x328x17 cm
<b>Max Load:</b>	30 kg per screen
<b>Pillar length:</b>	Min: 580mm to Max: 1550 mm from ceiling to VESA plate center Extension pipes: 3m (1500mm*2pcs) included
<b>Tilt:</b>	Yes, 0~15°
<b>Swivel:</b>	Yes, 360°
<b>Rotate:</b>	Yes, ±4°
<b>Cable Management:</b>	Yes
<b>Options:</b>	Extension pipes : 0.8m, 1.5m, 3.0m
<b>Certifications:</b>	CE
<b>Warranty:</b>	5 years

### Retail Package Specification

<b>Package Parcels:</b>	1 pcs
<b>Package Measurements:</b>	151.6 x 17.7 x 28.8 cm
<b>Package Weight:</b>	13.80 kg

The content of this specification is subject to change without further notice. Always visit our web for the latest updated specifications. <https://products.multibrackets.com/>