



SMART IC
 INTELLIGENTE LADESTEUERUNG
 INTELLIGENT CHARGE CONTROL

Produktname | *Product name*: Home Charger 231+
 Artikelnummer | *Part Number*: 1001-0067
 Ersteller / Datum | *Creator / Date*: DE / 26.10.2017

Version	Change	Date	Name
V0	---	26.10.2017	DE


Template name: USB-cable , Template version: V0

Technische Daten des Adapters / technical data of the adapter:



Eingang / Primär:		<i>input / primary:</i>	
Spannung	100-240V AC 50z/60Hz	voltage	100-240V AC 50z/60Hz
Strom	max. 500mA	current	max. 500mA
Ausgang / Sekundär:		<i>output / secondary:</i>	
Spannung	5.0V DC $\pm 5\%$	voltage	5.0V DC $\pm 5\%$
Strom (Port)	max. 3100mA (2400mA)	current (Port)	max. 3100mA (2400mA)
Leistung	15.5W	power	15.5W
USB Port	2 x Type A USB	USB port	2 x Type A USB
USB Beschaltung	smart IC	USB resistor network	smart IC
Schutzbeschaltung		<i>protection circuit</i>	
	Kurzschlusschutz Überspannungsschutz Verpolschutzschutz		short circuit protection over voltage protection wrong polarity protection
Gehäuse		<i>case</i>	
	Steckergehäuse schwarz		plug-in case black
Gehäusematerial		<i>housing material</i>	
	UL94V-0		UL94V-0
Betriebstemperatur		<i>operating temperature</i>	
	0°C.....+40°C		0°C.....+40°C
Approbation		<i>approval</i>	
	CE		CE
Gewicht ohne Verpackung		<i>weight without package</i>	
	87g		87g
Verpackung		<i>package</i>	
	Farbige Faltschachtel		color box
Lieferumfang		<i>delivery</i>	
	-USB Kabel 100cm ± 1 cm 2in1 Micro/Type-C -Anleitung(Sicherheitshinweis)		-USB cable 100cm ± 1 cm 2in1 Micro/Type-C -manual(safety instruction)

2D Zeichnung / Drawing:



Allowable deviation / general tolerances DIN ISO 2768-c