

PG & Metric Nylon Cable Glands

Product Type:

PG & Metric Cable Glands

Standards:

UL certified
IP68 ingress protection

Application:

Nylon cable glands made from Polyamide 6. Includes locknut and available in both metric and PG thread versions. Available in a range of popular sizes and in colours, red, white, black and grey.



PG Nylon Cable Gland Pack

Complete with Locknuts fitted

Part No.	Replace * for Col.		Thread Size	Cable Diameter	Overall Length	Pack Qty
	Black	Grey				
ACGP7*	BLK	GRY	PG7	3.0-6.5mm	15mm	10
ACGP9*	BLK	GRY	PG9	4.0-8.0mm	19mm	10
ACGP11*	BLK	GRY	PG11	5.0-10.0mm	22mm	10
ACGP135*	BLK	GRY	PG13.5	6.0-12.0mm	27mm	10
ACGP16*	BLK	GRY	PG16	10.0-14.0mm	27mm	10
ACGP21*	BLK	GRY	PG21	13.0-18.0mm	33mm	10
ACGP29*	BLK	GRY	PG29	18.0-25.0mm	42mm	10
ACGP36*	BLK	GRY	PG36	22.0-32.0mm	53mm	5
ACGP42*	BLK	GRY	PG42	30.0-38.0mm	60mm	5

Metric Nylon Cable Gland Pack

Complete with Locknuts fitted and Washer

Part No.	Replace * for Col.					Thread Size	Cable Diameter	Overall Length	Pack Qty
	Black	Grey	Red	White	Blue				
ACGM12*	BLK	GRY	RED	WHT		12	3.0-6.5mm	15mm	10
ACGM16*	BLK	GRY	RED	WHT		16	5.0-10.0mm	22mm	10
ACGM20*	BLK	GRY	RED	WHT		20	6.0-12.0mm	24mm	10
ACGM20L*	BLK	GRY	RED	WHT	BLUE	20	10.0-14.0mm	27mm	10
ACGM25*	BLK	GRY	RED	WHT		25	13.0-18.0mm	33mm	10
ACGP32*	BLK	GRY	RED	WHT		32	18.0-25.0mm	42mm	10
ACGP40*	BLK	GRY	RED	WHT		40	22.0-32.0mm	53mm	5
ACGP50*	BLK	GRY	RED	WHT		50	30.0-38.0mm	60mm	5
ACGP63*	BLK	GRY	RED	WHT		63	34.0-44.0mm	65mm	5