

Low Smoke BW & CW Gland Kits

Product Type:

Low Smoke BW & CW Gland Kits

Standards:

CW are waterproof to standards IP66 on inner and outer seal
Manufactured to BS6121 Part 1

Application:

BW and CW cable glands, suitable for securing most rubber and plastic coated cables to electrical sources. The cables come complete with a locking nut offering positive armour locking and effective earth continuity. Can be used in corrosive conditions when used with shroud. The shrouds are low smoke fume.



Low Smoke BW Gland Kits

Code	Description	Pack Qty
ABW20S-LSF	Brass cbl gland 20mm 2 Pt Kt	2
ABW20-LSF	Brass cbl gland 20mm 2 Pt Kt	2
ABW25-LSF	Brass cbl gland 25mm 2 Pt Kt	2
ABW32-LSF	Brass cbl gland 32mm 2 Pt Kt	2
ABW40-LSF	Brass cbl gland 40mm 2 Pt Kt	1
ABW50S-LSF	Brass cbl gland 50mm 2 Pt Kt	1
ABW50-LSF	Brass cbl gland 50mm 2 Pt Kt	1
ABW63S-LSF	Brass cbl gland 63mm 2 Pt Kt	1
ABW63-LSF	Brass cbl gland 63mm 2 Pt Kt	1
ABW75S-LSF	Brass cbl gland 75mm 1 Pt Kt	1
ABW75-LSF	Brass cbl gland 75mm 1 Pt Kt	1



Low Smoke CW Gland Kits

Code	Description	Pack Qty
ACW20S-LSF	Brass cbl gland 20mm 2 Pt Kt	2
ACW20-LSF	Brass cbl gland 20mm 2 Pt Kt	2
ACW25-LSF	Brass cbl gland 25mm 2 Pt Kt	2
ACW32-LSF	Brass cbl gland 32mm 2 Pt Kt	2
ACW40-LSF	Brass cbl gland 40mm 1 Pt Kt	1
ACW50S-LSF	Brass cbl gland 50mm 1 Pt Kt	1
ACW50-LSF	Brass cbl gland 50mm 1 Pt Kt	1
ACW63S-LSF	Brass cbl gland 63mm 1 Pt Kt	1
ACW63-LSF	Brass cbl gland 63mm 1 Pt Kt	1
ACW75S-LSF	Brass cbl gland 75mm 1 Pt Kt	1
ACW75-LSF	Brass cbl gland 75mm 1 Pt Kt	1