

Lenovo V130 (15") 81HN00FA++

Product
Lenovo V130-15IKB

Region
EMEA

Machine Type
81HN

Processor
Core i5-7200U (2C, 2.5 / 3.1GHz, 3MB)

Graphics
Integrated Intel HD Graphics 620

Memory
4GB Soldered + 4GB DIMM

Display
15.6" FHD (1920x1080)

Multi-touch
None

Storage
256GB SSD M.2

Optical
DVD±RW

Ethernet
100/1000M

WLAN + Bluetooth
11ac, 1x1 + BT4.1

Color
Iron Grey

Camera
720p

Microphone
Monaural

Keyboard
Non-backlit

Fingerprint Reader
None

Battery
2-cell (30Wh)

Power Adapter
45W

Operating System
Windows 10 Home 64

Warranty
1-year, Depot

Ann Date (mm/yy)
04/18

Note:

* Country Code "US" is for United States, "++" is for EMEA countries (e.g. AD - Saudi, Arabia, AT - Austria, BM - Bulgaria, etc.), "xx" is for EAST countries (e.g. BM - Bulgaria, CX - Hungary, CY - Cyprus, etc.), and "***" is for MEA countries (e.g. AD - Saudi, Arabia, ED - Egypt, EQ - Sweden, etc.). Please be aware that the EMEA/ EAST/MEA models listed above might not be available in all countries



WWW.LENOVO.COM

This publication was developed for products and services offered in the United States and E.M.E.A countries. Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors.

Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<http://psref.lenovo.com>

Visit psref website for the latest version of Product Specifications Reference.

© Lenovo, 2017. All rights reserved.

Lenovo™

Lenovo V130 (15") Platform Specifications

Product Specifications Reference (PSREF)



Processor	V130-15IGM: Intel® Celeron® Processor, Intel Pentium® Silver Processor							Ethernet	Gigabit Ethernet connection	
	Processor Number	# of Cores	# of Threads	Base Frequency	Burst Frequency	Cache	Memory Types	Processor Graphics	WLAN Bluetooth™	11ac, 1x1, Wi-Fi + Bluetooth combo adapter, M.2 Card Bluetooth 4.1 wireless, integrated in Wi-Fi + Bluetooth combo adapter
	Cel N4000	2	2	1.1 GHz	2.6 GHz	4MB	DDR4-2400	Intel UHD Graphics 600	Dimensions	WxDxH: 14.76" x 9.96" x 0.88"; 375mm x 253mm x 22.3mm
	Cel N4100	4	4		2.4 GHz			Intel UHD Graphics 605	Weight	V130-15IGM: Start weight at 1.85kg (4.08lb)
	Pen N5000				2.7 GHz			Case color	V130-15IKB: Start weight at 1.80kg (3.97lb)	
	V130-15IKB: Intel Celeron Processor, Intel Pentium Silver Processor, 7th Generation Intel Core i3 / i5 Processor							Case material	Iron Gray PC/ABS plastic	
	Processor Number	# of Cores	# of Threads	Base Frequency	Max Turbo Frequency	Cache	Memory Types	Processor Graphics	Media reader	4-in-1 reader (MMC, SD, SDHC, SDXC)
	Cel 3865U	2	4	1.8 GHz	-	2MB	DDR4-2133	Intel HD Graphics 610	Ports	V130-15IGM: One USB 3.0, one USB 2.0, HDMI, Ethernet (RJ-45) V130-15IKB: Two USB 3.0, HDMI, Ethernet (RJ-45)
	Pen 4415U			2.3 GHz	-	2MB		Intel HD Graphics 620		
	i3-7020U			2.3 GHz	-	3MB				
	i5-7200U			2.5 GHz	3.1 GHz	3MB				
Graphics	V130-15IGM: Intel UHD Graphics 600 or 605 in processor only; V130-15IKB: Intel HD Graphics 610 or 620 in processor only, or Intel HD Graphics 610 or 620 in processor and AMD Radeon 530, 2GB memory; supports three independent displays; Max resolution: 4096x2304@24Hz (HDMI);							Camera (optional)	0.3MP or 720p, fixed focus, camera cover	
Chipset	Intel SoC (System on Chip) platform							Audio support	Stereo speakers with Dolby® Audio™, 2W x 2 / optional monaural digital microphone, combo audio/microphone jack	
Memory	V130-15IGM: 8GB max / 2400MHz DDR4, one DDR4 SO-DIMM socket V130-15IKB: 12GB max / 2133MHz DDR4, dual-channel capable, 4GB memory soldered to systemboard, one DDR4 SO-DIMM socket * System clocks down for processors with lower memory controller							Keyboard	6-row, multimedia Fn keys, numeric keypad, spill-resistant	
Display	Some: 15.6" (396mm) HD (1366x768), anti-glare, LED backlight, 220 nits, 16:9 aspect ratio Some: 15.6" (396mm) FHD (1920x1080), anti-glare, LED backlight, 220 nits, 16:9 aspect ratio							Touchpad	Clickpad, multi-touch	
Multi-touch	None							Security	Power-on password, hard disk password, supervisor password, security keyhole	
Storage	Some: M.2 SSD / PCIe 3.0 x 4 NVMe or SATA 6.0Gb/s (V130-15IKB Core i only) Some: M.2 SSD / PCIe 3.0 x 2 NVMe or SATA 6.0Gb/s (V130-15IKB Core i only) Some: SSD / SATA 6.0Gb/s, 2.5" wide (V130-15IGM only) Some: HDD / SATA 6.0Gb/s, 2.5" wide, 7mm high							Security chip	Firmware TPM 2.0, integrated in chipset	
SATA controller	Serial ATA, SATA 6.0Gb/s support, integrated in processor							Fingerprint reader	None	
Optical (optional)	DVD burner, 9.0mm high, fixed, not removable, tray-in							Internal battery	Integrated Li-Ion 2-cell (30Wh)	
								External battery	None	
								Max battery life	Up to 6 hours (MobileMark® 2014)	
								AC adapter	V130-15IGM: 45W AC adapter V130-15IKB: 45W or 65W AC adapter	
								Preload	Some: Windows 10 Home 64 Some: Windows 10 Pro 64 • Lenovo Companion • Lenovo Setting • Microsoft Office preloaded purchase a product key to activate • McAfee® LiveSafe™ (30-day trial)	
								Limited warranty	One of the following, configurable by model: • 1-year depot repair service • 2-year/1-yr battery depot repair service	
								Environment	EPEAT™ Silver; ENERGY STAR® 6.1; RoHS-compliant	

Lenovo V130 (15")

