

HP 250 G6(3QM23EA#ABU)

HP 250 G6 - Core i3 7020U / 2.3 GHz - Win 10 Pro 64-bit - 4 GB RAM - 500 GB HDD - DVD-Writer - 15.6" TN 1366 x 768 (HD) - HD Graphics 620 - Wi-Fi,Bluetooth - dark ash silver,fresh woven texture,jet black (keyboard) - kbd:UK



Get connected with the HP 250 notebook PC. Complete business tasks with advanced technology and essential collaboration tools loaded on the HP 250. The durable chassis helps protect the notebook from the rigors of the day.

Key Selling Points

Durable mobile design
Powered for business
Hassle-free connectivity

Product Features

Durable mobile design

Rest assured that the HP 250 can keep up with assignments on the run. The durable chassis protects the notebook so it looks as professional as you do.

Powered for business

Confidently complete projects with the power advanced processors.

Let nothing stand in your way

Help secure the future of your business. PCs from HP protect you from security threats and maximize management and productivity features for business.

Main Specifications

Product Description	HP 250 G6 - 15.6"- Core i3 7020U - 4 GB RAM - 500 GB HDD - UK
Product Type	Notebook
Operating System	Win 10 Pro 64-bit - English
Processor	Intel Core i3 (7th Gen) 7020U / 2.3 GHz / 3 MB Cache
Memory	4 GB DDR4
Storage	500 GB HDD / 5400 rpm
Optical Drive	DVD-Writer
Display	15.6"WLED 1366 x 768 / HD
Graphics	Intel HD Graphics 620
Numeric Keypad	Yes
Integrated Webcam	Yes
Networking	802.11a/b/g/n/ac,Bluetooth 4.2,Gigabit Ethernet
Security	Firmware Trusted Platform Module (TPM 2.0) Security Chip
Colour	Dark ash silver,fresh woven texture,jet black (keyboard)
Dimensions (WxDxH)	38 cm x 25.38 cm x 2.38 cm
Weight	1.86 kg
Localisation	Language: English / region: United Kingdom
Environmental Standards	ENERGY STAR Qualified
Manufacturer Warranty	Limited warranty - 1 year Limited warranty - battery - 1 year

Extended Specification

General

Product Type	Notebook
Operating System	Windows 10 Pro 64-bit Edition - English

Processor / Chipset

CPU	Intel Core i3 (7th Gen) 7020U / 2.3 GHz
Number of Cores	Dual-Core
Cache	3 MB
64-bit Computing	Yes
Features	Hyper-Threading Technology, Intel Smart Cache

Memory

RAM	4 GB
Max RAM Supported	8 GB
Technology	DDR4 SDRAM
Speed	2133 MHz - 2133 MHz
Form Factor	SO-DIMM 260-pin

Storage

Main Storage	500 GB HDD SATA 6Gb/s / 5400 rpm
Optical Drive	DVD-Writer

Display

Type	15.6" - TN
LCD Backlight Technology	WLED backlight
Resolution	1366 x 768 (HD)
Widescreen	Yes
Image Brightness	220 cd/m ²
Features	Slim Design, HD standard-viewing angle (SVA) eDP anti-glare

Audio & Video

Graphics Processor	Intel HD Graphics 620
Camera	Yes - VGA
Video Resolutions	640 x 480
Frame Rate	30 frames per second
Sound	Stereo speakers, array microphone

Input

Type	Keyboard, touchpad
Keyboard Layout	UK
Numeric Keypad	Yes
Features	Multi-touch touchpad, touchpad with gesture support

Communications

Wireless	802.11a/b/g/n/ac,Bluetooth 4.2
Bluetooth Class	Class 2
Wireless Controller	Intel Dual Band Wireless-AC 3168 - PCI Express Mini Card (M.2)
Network Interface	Gigabit Ethernet
Features	Miracast
Compliant Standards	IEEE 802.11,IEEE 802.3ab,IEEE 802.1x,IEEE 802.11i,Wi-Fi CERTIFIED

Battery

Technology	Lithium Ion
------------	-------------

AC Adapter

Input	AC 120/230 V (50/60 Hz)
Output	19.5 V

Connections &Expansion

Interfaces	VGA HDMI Headphone/microphone combo jack LAN 2 x USB 3.1 Gen 1 USB 2.0
Memory Card Reader	Yes (SD Card,SDHC Card,SDXC Card)

Miscellaneous

Colour	Dark ash silver,fresh woven texture,jet black (keyboard)
Security	Firmware Trusted Platform Module (TPM 2.0) Security Chip
Features	HP Fast Charge
Theft/Intrusion Protection	Security lock slot (cable lock sold separately)
Security Slot Type	Kensington security slot
Included Accessories	Power adapter
Localization	Language: English / region: United Kingdom

Dimensions &Weight

Dimensions (WxDxH)	38 cm x 25.38 cm x 2.38 cm
Weight	1.86 kg

Environmental Standards

ENERGY STAR Certified	Yes
-----------------------	-----

Manufacturer Warranty

Service &Support	Limited warranty - 1 year Limited warranty - battery - 1 year
------------------	--

Product data is provided by CNET,we do not warrant the accuracy and completeness of the material contained in this data sheet