

KRM55WR7YA336MH01#


"#" indicates a package specification code.



< List of part numbers with package codes >

KRM55WR7YA336MH01L , KRM55WR7YA336MH01K

Shape



L size	6.1 ±0.4mm
W size	5.3 ±0.2mm
T size	6.4 ±0.3mm
Metal terminal width e	1.2±0.2mm

References

Packaging	Specifications	Minimum quantity
L	φ 180mm Embossed taping	200
K	φ 330mm Embossed taping	500

Mass (typ.)	
1 piece	0.85g

Specifications

Capacitance	33μF ±20%
Rated voltage	35Vdc
Temperature characteristics (complied standard)	X7R(EIA)
Capacitance change rate	±15%
Temperature range of temperature characteristics	-55 to 125°C
Operating temperature range	-55 to 125°C

⚠ Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.