

315MHz Pendant RF Transmitters

- SK-919T1-GBQ** 1 Button, 1 Channel
- SK-919T1-GBUQ** 1 Button, 1 Channel, No logo
- SK-919T2-GNQ** 2 Buttons, 3 Channels
- SK-919T3-GNQ** 3 Buttons, 7 Channels
- SK-919T4-GNQ** 4 Buttons, 15 Channels

Features:

- Over 68 billion possible codes
- LED transmission indicator only appears when buttons are pressed
- Operates up to 500ft (150m)*
- RF Anti-scan protection
- FCC, IC, and CE Certified
- 315MHz (433.92MHz available)
- Compatible with all 315MHz SECO-LARM receivers
- Slimline design: 1 1/4"x2 3/16"x5/16" (31.5x55x8 mm)
- CODEBUMP™ codehopping models also available
- Replacement batteries available: X-930-096 (CR2032)
- Patented design



- Over 68 Billion Codes
- FCC Certified
- LED Indicator
- Up to 500ft*

Typical Applications:



OEM / ODM Private Label Available:



- Convert your product to wireless control
- All products above are FCC and IC certified to bring your products to market faster (other models available with CE)
- We can provide custom colors, labels, icons, button configurations, and cases, all with your own logo
- Contemporary matching design allows for easy scalability as your product line expands

*Actual range will vary greatly depending on the installation and operating environment