

PRODUCT Data

HARVARD MODEL NO	GDSB05BT1000P
PRODUCT DESCRIPTION	Bluetooth 100w Soundbar inc built in subwoofer
PRODUCT CATEGORY	SOUNDBAR
COLOUR	BLACK
COUNTRY OF ORIGIN	CHINA
BARCODES (EAN-ITF)	5018379112090
	05018379112106

PRODUCT Specification

High power 2.1CH TV sound bar Speaker System
 Output power : Subwoofer at 60W + Satellite at 20W x 2 Watts , total : 100W
 Built-in bluetooth receiver
 control buttons :Power, Source/Pairing, Volume+ and Volume-
 3 bands EQ (Movie, Music and Voice)
 digital LED display
 Full function remote control
 Desk-top placement or wall mount options
 AC/DC power adaptor (24V, 2.5A)

PRODUCT Technical Specification

POWER OUTPUT	100w	MAINS / BATTERY	AC
DISPLAY TYPE	LED	BATTERY	
DAB (Y/N)	N	TYPE UNIT	N
BLUETOOTH	Y	TYPE RC	1 x CR2025
MEDIA TYPE	N/A		
EQ	Y	CONNECTIONS	
HEADPHONE SOCKET	Y	TYPE	RCA
CLOCK FUNCTION	N		3.5mm JACK
ALARM FUNCTION	N		HDMI ARC
			OPTICAL in



PRODUCT Features & Benefits




ACCESSORIES (Whats in the box)

- IB (one language)
- QSG
- Safety & guarantee booklet
- Power Cable
- Remote Control
- RCA Cable
- 3.5mm Cable
- Optical Cable
- Wallmount Kit

DIMENSIONS

DISTRIBUTION FILL (@ 1.5M)		CONTAINER FILL		UNIT DIMS	LENGTH (CM)	WIDTH (CM)	HEIGHT (CM)	NET WEIGHT (KG)	GROSS WEIGHT (KG)
UNITS PER CARTON	2			PACKING INFORMATION					
TI		20' FCL	1200	UNIT	95.00	6.40	10.20	N/A	
HI		40' FCL	2470	GIFT BOX				N/A	
PALLET	0	40' HQ FCL	2860	SHIPPER CARTON					



WASTE PACKING INFORMATION

TOTAL PER SHIPPER CARTON	PAPER		STEEL	
	GLASS		PLASTIC	
	METAL		WOOD	
	ALUMINIUM		OTHER	

details are correct at time of print and subject to change