


KEMET, R11, Acoustic Module, Multilayer



Dimensions	
<b>L</b>	23.6mm MAX
<b>W</b>	4mm MAX
<b>T</b>	1.9mm MAX

Packaging Specifications	
<b>Weight:</b>	1.2
<b>Packaging:</b>	Bulk Tray, Box
<b>Packaging Quantity:</b>	1000

General Information	
<b>Style:</b>	Rubber Cased
<b>Description:</b>	Multilayer Piezoelectric Bimorph Actuator
<b>RoHS:</b>	Yes
<b>REACH:</b>	Yes

Specifications	
<b>Series:</b>	R11
<b>Capacitance:</b>	1 uF
<b>Capacitance Tolerance:</b>	20%
<b>Maximum Driving Voltage:</b>	25 V Peak-Peak
<b>Resonant Frequency:</b>	6 kHz
<b>Temperature Range:</b>	-25/+70C

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.