


KEMET Part Number: SBCP-80HY101H
(SBCP80HY101H)

KEMET, SBCP-80HY, Power, 100 uH, 10%, 5mm



Dimensions

D	9.5mm MAX
L	11mm MAX
S	5mm +/-0.5mm
LL	3.5mm +/-0.5mm
F	0.6mm NOM

Packaging Specifications

Weight:	2.06 g
Packaging:	T&R
Packaging Quantity:	2000

General Information

Series:	SBCP-80HY
Style:	Through-Hole
Description:	Radial Leaded, Ferrite Power Inductors
Features:	DC-DC Converters, Nickel-Zinc (NiZn) Ferrite Core
RoHS:	Yes
Lead:	Wire Leads
Core:	Ferrite
Notes:	Contains 4 Reels of 500 pieces each

Specifications

Inductance:	100 uH (0.01 MHz)
Inductance Tolerance:	10%
Temperature Range:	-20/+105C
Shielded:	No
Current:	1.1 Amps
DC Resistance:	0.35 Ohms