

**Basic**

Brand Name: Acer  
Environmentally Friendly: Yes  
Graphics Controller: Intel  
Manufacturer:  
Graphics Controller Model: HD Graphics 630  
Graphics Memory: Shared  
Accessibility:  
Graphics Memory Technology: DDR4 SDRAM  
HDMI: Yes  
Number of USB 2.0 Ports: 4  
Operating System: 64-bit  
Architecture:  
Operating System Platform: Windows  
Operating System: Windows 10 Pro  
Optical Drive Type: DVD-Writer  
Processor Manufacturer: Intel  
Processor Model: i3-7100  
Processor Speed: 3.90 GHz  
Processor Type: Core i3  
Product Family: Veriton ES2710G  
Product Type: Desktop Computer  
Standard Memory: 4 GB  
Total Hard Drive Capacity: 1 TB  
Total Number of USB Ports: 6  
VGA: Yes

**Display & Graphics**

Graphics Controller: Intel  
Manufacturer:  
Graphics Controller Model: HD Graphics 630  
Graphics Memory: Shared  
Accessibility:  
Graphics Memory Technology: DDR4 SDRAM  
TV Card: No

**General Information**

Brand Name: Acer  
Manufacturer Part Number: DT.VQEEK.017  
Manufacturer Website: <http://www.acer.co.uk>  
Address:  
Manufacturer: Acer, Inc  
Product Line: Veriton  
Product Name: Veriton ES2710G Desktop Computer  
Product Series: ES2710G  
Product Type: Desktop Computer

**I/O Expansions**

Number of PCI Express x16 Slots: 1  
Number of Total Expansion Slots: 1

**Input Devices**

Keyboard Type: Physical Keyboard  
Keyboard: Yes  
Pointing Device Type: Mouse

**Interfaces/Ports**

Audio Line In: Yes  
Audio Line Out: Yes  
HDMI: Yes  
Network (RJ-45): Yes  
Number of USB 2.0 Ports: 4  
Number of USB 3.1 Gen 1 Ports: 2  
Total Number of USB Ports: 6  
VGA: Yes

**Memory**

Maximum Memory: 32 GB  
Memory Card Reader: No  
Memory Standard: DDR4-2400/PC4-19200  
Memory Technology: DDR4 SDRAM  
Standard Memory: 4 GB

## Miscellaneous

Certifications & Standards:	<ul style="list-style-type: none"><li>• DMI</li><li>• GS</li><li>• PC2001</li><li>• BSMI</li><li>• VCCI</li><li>• CE</li><li>• FCC</li><li>• CB</li></ul>
Environmental Certification:	RoHS
Environmentally Friendly:	Yes
Features:	Security Slot
Package Contents:	<ul style="list-style-type: none"><li>• Veriton ES2710G Desktop Computer</li><li>• USB Keyboard</li><li>• USB Mouse</li></ul>

## Network & Communication

Ethernet Technology:	Gigabit Ethernet
Modem:	No

## Physical Characteristics

Depth:	320 mm
Height:	340 mm
Weight (Approximate):	8 kg
Width:	165 mm

## Power Description

Maximum Power Supply Wattage:	220 W
-------------------------------	-------

## Processor & Chipset

64-bit Processing:	Yes
Cache:	3 MB
Chipset Manufacturer:	Intel
Chipset Model:	H110 Express
Number of Processors Installed:	1
Number of Processors Supported:	1
Processor Core:	Dual-core (2 Core)
Processor Generation:	7th Gen
Processor Manufacturer:	Intel
Processor Model:	i3-7100
Processor Speed:	3.90 GHz
Processor Type:	Core i3

## Software

Operating System Architecture:	64-bit
Operating System Platform:	Windows
Operating System:	Windows 10 Pro

## Storage

Dual-Layer Media Supported:	Yes
Hard Drive Configuration:	1 x 1 TB
Hard Drive Interface:	Serial ATA/600
Hard Drive RPM:	7200
Number of Hard Drives:	1
Optical Drive Type:	DVD-Writer
Optical Media Supported:	DVD-RAM/±R/±RW
Total Hard Drive Capacity:	1 TB