


GoldMax 300 Comm Z5U, Ceramic, 4.7 uF, 20%, 50 VDC, Z5U, GoldMax, Commercial Standard, Lead Spacing = 10.16mm



**Dimensions**

<b>L</b>	8.38mm MAX
<b>H</b>	10.16mm MAX
<b>T</b>	5.08mm MAX
<b>S</b>	10.16mm +/-0.78mm
<b>LL</b>	7mm MIN
<b>F</b>	0.64mm +0.1/-0.025mm

**Packaging Specifications**

<b>Packaging:</b>	Bulk, Bag
<b>Packaging Quantity:</b>	50

**General Information**

<b>Supplier:</b>	KEMET
<b>Series:</b>	GoldMax 300 Comm Z5U
<b>Style:</b>	Radial
<b>Description:</b>	GoldMax, Commercial Standard
<b>RoHS:</b>	Yes
<b>Termination:</b>	Tin
<b>Failure Rate:</b>	N/A
<b>Halogen Free:</b>	Yes

**Specifications**

<b>Capacitance:</b>	4.7 uF
<b>Capacitance Tolerance:</b>	20%
<b>Voltage DC:</b>	50 VDC
<b>Dielectric Withstanding Voltage:</b>	125 V
<b>Temperature Range:</b>	-10/+85C
<b>Temperature Coefficient:</b>	Z5U
<b>Dissipation Factor:</b>	4.00% 25C
<b>Aging Rate:</b>	7% Loss/Decade Hour
<b>Insulation Resistance:</b>	20 MOhms