

**KEMET Part Number: CDR01BP150BJZR-T&R**  
(C0805P150J1GRL7189)

SMD Mil PRF55681, Ceramic, Military/High Reliability, 15 pF, 5%, 100 VDC, BP, R (0.01%/1000 Hrs), 0805




**Dimensions**

<b>L</b>	2.03mm +/-0.38mm (0.08 in +/-0.015 in)
<b>W</b>	1.27mm +/-0.38mm (0.05 in +/-0.015 in)
<b>T</b>	0.98mm +/-0.42mm (0.039 in +/-0.017 in)
<b>B</b>	0.51mm +/-0.25mm (0.02 in +/-0.01 in)

**Packaging Specifications**

<b>Packaging:</b>	T&R, 178mm, Plastic Tape
<b>Packaging Quantity:</b>	2500

**General Information**

<b>Supplier:</b>	KEMET
<b>Series:</b>	SMD Mil PRF55681
<b>Style:</b>	SMD Chip
<b>RoHS:</b>	No
<b>Prop 65:</b>	 <b>WARNING:</b> Cancer and reproductive harm - <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>
<b>REACH:</b>	SVHC (Pb – CAS 7439-92-1)
<b>Termination:</b>	Lead (SnPb)
<b>Failure Rate:</b>	R (0.01%/1000 Hrs)
<b>Testing and Reliability:</b>	MIL-PRF-55681
<b>Qualifications:</b>	MIL-PRF-55681
<b>Miscellaneous:</b>	Termination Description: SolderPlate 70-30
<b>Chip Size:</b>	0805

**Specifications**

<b>Capacitance:</b>	15 pF
<b>Capacitance Tolerance:</b>	5%
<b>Voltage DC:</b>	100 VDC
<b>Temperature Range:</b>	-55/+125C
<b>Temperature Coefficient:</b>	BP