



[Accessory Guide](#) / [Fan Cords](#) / [Mounting Clips](#)

## ACCESSORY GUIDE

	Part No.	1606KL	2408NL	2410ML	3108NL	3110KL	3610KL	4710NL
Fan Guards	055010							
	055011							
	055013						x	
	055015							x
	055018				x	x		
	055019				x	x		
	055023		x	x				
	055025	x						
Mounting Clips	512011							
	512020							
	512021							
	512023							
Cord Sets	432000							
	432002							

	432021							
--	--------	--	--	--	--	--	--	--

TOP ▲

	Part No.	4715KL	5920PL	6820PL	2412PS	3110PS	3115PS	3115FS
Fan Guards	055010		x	x				
	055011		x	x				
	055013							
	055015	x						
	055018					x	x	x
	055019					x	x	x
	055023				x			
	055025							
Mounting Clips	512011							
	512020							
	512021							x
	512023					x		
Cord Sets	432000					x	x	x
	432002					x	x	x
	432021					x	x	x

TOP ▲

	Part No.	3610PS	4710PS	4715MS	4715FS	5915P
Fan Guards	055010					x
	055011					x
	055013	x				
	055015		x	x	x	
	055018					
	055019					
	055023					
	055025					
Mounting Clips	512011				x	
	512020					

	512021		x			
	512023					
Cord Sets	432000	x	x	x	x	x
	432002	x	x	x	x	x
	432021	x	x	x	x	x


[TOP ▲](#)

## FAN CORDS [Straight Style](#) / [90 Degree Style](#)


- Comply with UL, CSA, and VDE requirements
- Ratings: UL Rated 10 AMP/125 VA CSA Rated 7 AMP/125 VAC
- Constructed from 2 conductor 18 AWG SPT-1 105 C VW-1
- Straight and 90 degree style plugs available

Cord Sets	Length	Model No.
Straight Style	24"	432000
	36"	432020
	48"	432002
90 degree	36"	432021

### Straight Style



### 90 Degree Style




[TOP ▲](#)

## MOUNTING CLIPS


**512020**

3115FS Series




**512021**

4710PS Series 3110PS Series



**512011**

4715FS Series



**512023**

4715KL Series

