


**KEMET Part Number: GMC16.5225K100C31TR24**  
(F115ZS225K100V)

GMC/F115, Film, Metallized PEN, General Purpose, 2.2 uF, 10%, 63 VAC, 100 VDC, 100C, 6560, 7mm



Note: '()' correspond to the letters used in the product bulletin

Dimensions	
Chip Size	6560
L	16.5mm +/-0.2mm
W	15mm +/-0.2mm
T	7mm +/-0.2mm
F	0.5mm NOM

Packaging Specifications	
Packaging:	T&R
Packaging Quantity:	500

General Information	
Supplier:	KEMET
Series:	GMC/F115
Dielectric:	Metallized PEN
Style:	SMD Chip
RoHS:	Yes

Specifications	
Capacitance:	2.2 uF
Capacitance Tolerance:	10%
Voltage AC:	63 VAC
Voltage DC:	100 VDC
Temperature Range:	-55/+125C
Rated Temperature:	100C
Dissipation Factor:	0.60% 1kHz, 1.00% 10kHz
Insulation Resistance:	1.3636 GOhms
Max dV/dt:	8 V/us