


KEMET Part Number: 050MS22AAMA1STD
(A902GF050V220A)

MS/A902, Aluminum Electrolytic, Motor Start, 50 uF, -0/+25%, 220 VAC, -20/+60C



| Dimensions | |
|------------|---------------|
| D | 38mm +/-0.5mm |
| L | 75mm MAX |

| Packaging Specifications | |
|--------------------------|-----------|
| Packaging: | Bulk, Bag |

| General Information | |
|---------------------|-----------------------------------|
| Supplier: | KEMET |
| Series: | MS/A902 |
| Dielectric: | Aluminum Electrolytic |
| Description: | Motor Start Aluminum Electrolytic |
| RoHS: | Yes |
| Lead: | Quick Connect |
| Shelf Life: | 156 Weeks |

| Specifications | |
|------------------------|----------|
| Capacitance: | 50 uF |
| Capacitance Tolerance: | -0/+25% |
| Voltage AC: | 220 VAC |
| Temperature Range: | -20/+60C |
| Rated Temperature: | 60C |
| Life: | 500 Hrs |