

KEMET Part Number: SMR10105J63A04L16.5CBULK
(F211AP105J063ALG5C)

SMR/F211, Film, Metallized PPS, General Purpose, 1 uF, 5%, 63 VDC, 125C, Lead Spacing = 10mm



General Information	
Supplier:	KEMET
Series:	SMR/F211
Dielectric:	Metallized PPS
Style:	Radial
Features:	Audio Applications
RoHS:	Yes
Lead:	Wire Leads
Miscellaneous:	The rated voltage decreases 2%/C between +125C and +150C
Notes:	Case Size = AP

Dimensions	
L	13mm MAX
H	12mm MAX
T	6mm MAX
S	10mm +/-0.4mm
LL	16.5mm +0.5mm
F	0.6mm +/-0.05mm
G	0.5mm NOM

Specifications	
Capacitance:	1 uF
Capacitance Tolerance:	5%
Voltage AC:	40 VAC
Voltage DC:	63 VDC
Temperature Range:	-55/+150C
Rated Temperature:	125C
Dissipation Factor:	0.15% 1kHz, 0.25% 10kHz, 0.6% 100kHz
Insulation Resistance:	5 GOhms
Max dV/dt:	8 V/us

Packaging Specifications	
Packaging:	Bulk, Bag
Packaging Quantity:	600