


KEMET Part Number: SMR15104J400B10L16.5CBULK
(F211BJ104J400ALG5C)

SMR/F211, Film, Metallized PPS, General Purpose, 0.1 uF, 5%, 400 VDC, 125C, Lead Spacing = 15mm



General Information	
Supplier:	KEMET
Series:	SMR/F211
Dielectric:	Metallized PPS
Style:	Radial
Features:	Audio Applications
RoHS:	Yes
Lead:	Wire Leads
Miscellaneous:	The rated voltage decreases 2%/C between +125C and +150C
Notes:	Case Size = BJ

Dimensions	
L	18mm MAX
H	12.5mm MAX
T	6.5mm MAX
S	15mm +/-0.4mm
LL	16.5mm +0.5mm
F	0.8mm +/-0.05mm
G	0.5mm NOM

Specifications	
Capacitance:	0.1 uF
Capacitance Tolerance:	5%
Voltage AC:	200 VAC
Voltage DC:	400 VDC
Temperature Range:	-55/+150C
Rated Temperature:	125C
Dissipation Factor:	0.15% 1kHz, 0.25% 10kHz, 0.5% 100kHz
Insulation Resistance:	30 GOhms
Max dV/dt:	15 V/us

Packaging Specifications	
Packaging:	Bulk, Bag
Packaging Quantity:	600