

C4AQ, Film, Metallized Polypropylene, Automotive DC Link, 1.5 uF, 5%, 1500 VDC, 70C, Lead Spacing = 27.5mm



General Information	
Supplier:	KEMET
Series:	C4AQ
Dielectric:	Metallized Polypropylene
Style:	Radial
RoHS:	Yes
Lead:	Wire Leads
Qualifications:	AEC-Q200, IEC61071, EN61071, VDE0560
AEC-Q200:	Yes
Miscellaneous:	Rth = 36 C/W

Dimensions	
L	31.5mm +/-0.5mm
H	25mm +/-0.2mm
T	13mm +/-0.3mm
S	27.5mm +/-0.4mm
LL	6mm +0/-2mm
F	0.8mm +/-0.05mm

Specifications	
Capacitance:	1.5 uF
Capacitance Tolerance:	5%
Voltage DC:	1500 VDC
Temperature Range:	-40/+105C
Rated Temperature:	70C
Dissipation Factor:	0.02% (10 kHz 25C)
Insulation Resistance:	20 Ohms
Max dV/dt:	31 V/us
Resistance:	17.7 mOhms (10kHz 70C)
Ripple Current:	4.5 Amps Irms (10kHz 70C), 49 Amps Ipk
Inductance:	25 nH

Packaging Specifications	
Packaging:	Bulk, Box
Packaging Quantity:	234