


C44P-R, Film, Metallized Polypropylene, AC Filter, 500 uF, 10%, 330 VAC, 700 VDC



Dimensions	
D	85mm +/-0.5mm
L	197mm +/-2mm
S	35mm +/-1mm

Packaging Specifications	
Mounting:	Bolt - M12x16
Packaging:	Bulk, Bag

General Information	
Supplier:	KEMET
Series:	C44P-R
Dielectric:	Metallized Polypropylene
Style:	Can
Features:	Single Phase PFC
RoHS:	Yes
Lead:	Threaded Studs M10
Miscellaneous:	Thermal Resistance = 3.4 C/W

Specifications	
Capacitance:	500 uF
Capacitance Tolerance:	10%
Voltage AC:	330 VAC
Voltage DC:	700 VDC
Temperature Range:	-25/+70C
Rated Temperature:	70C
Dissipation Factor:	0.02% 25C
Max dV/dt:	12.5 V/us
Resistance:	1.2 mOhms (10kHz)
Ripple Current:	63 Amps (10kHz 40C)
Inductance:	160 nH