


C44P-R, Film, Metallized Polypropylene, AC Filter, 22 uF, 10%, 640 VAC, 1400 VDC



Dimensions	
D	65mm +/-0.5mm
L	147mm +/-2mm
S	28mm +/-1mm

Packaging Specifications	
Mounting:	Bolt - M12x16
Packaging:	Bulk, Bag

General Information	
Supplier:	KEMET
Series:	C44P-R
Dielectric:	Metallized Polypropylene
Style:	Can
Features:	Single Phase PFC
RoHS:	Yes
Lead:	Threaded Studs M10
Miscellaneous:	Thermal Resistance = 10.9 C/W

Specifications	
Capacitance:	22 uF
Capacitance Tolerance:	10%
Voltage AC:	640 VAC
Voltage DC:	1400 VDC
Temperature Range:	-25/+70C
Rated Temperature:	70C
Dissipation Factor:	0.02% 25C
Max dV/dt:	30 V/us
Resistance:	2.996643906 mOhms (10kHz)
Ripple Current:	35 Amps (10kHz 40C)
Inductance:	125 nH