


C9T, Film, Metallized Polypropylene, AC Filter, 41.1 uF, -5/+15%, 440 VAC



**General Information**

<b>Supplier:</b>	KEMET
<b>Series:</b>	C9T
<b>Dielectric:</b>	Metallized Polypropylene
<b>Style:</b>	Can
<b>Features:</b>	Three Phase PFC
<b>RoHS:</b>	Yes
<b>Lead:</b>	Quick Connect
<b>Qualifications:</b>	VDE
<b>Miscellaneous:</b>	Q = 7.5 kvar. Operating Freq. = 50 Hz

**Dimensions**

<b>D</b>	75mm +/-0.5mm
<b>L</b>	160mm +/-2mm

**Packaging Specifications**

<b>Mounting:</b>	Bolt - M12x16
<b>Packaging:</b>	Bulk, Bag
<b>Packaging Quantity:</b>	12

**Specifications**

<b>Capacitance:</b>	41.1 uF
<b>Capacitance Tolerance:</b>	-5/+15%
<b>Voltage AC:</b>	440 VAC
<b>Temperature Range:</b>	-25/+55C
<b>Rated Temperature:</b>	55C
<b>Max dV/dt:</b>	30 V/us
<b>Ripple Current:</b>	13 Amps