


KEMET Part Number: PMR209MC6220M100R30
(P409CP224M250AH101)

PMR209/P409, Film, Metallized Paper, Resistor/Capacitor, 0.22 uF, 20%, 630 VDC, 85C, Lead Spacing = 20.3mm



Dimensions

| | |
|-----------|-----------------|
| L | 24mm MAX |
| H | 16.5mm MAX |
| T | 11.3mm MAX |
| S | 20.3mm +/-0.4mm |
| LL | 30mm +5mm |
| F | 0.8mm +/-0.05mm |

Packaging Specifications

| | |
|----------------------------|-----------|
| Packaging: | Bulk, Bag |
| Packaging Quantity: | 150 |

General Information

| | |
|------------------------|--|
| Supplier: | KEMET |
| Series: | PMR209/P409 |
| Dielectric: | Metallized Paper |
| Style: | Radial |
| Features: | RC Unit approved |
| RoHS: | Yes |
| Lead: | Wire Leads |
| Qualifications: | ENEC, UL, cUL |
| AEC-Q200: | No |
| Construction: | Molded |
| Miscellaneous: | Resistor= 100 Ohms |
| Notes: | Not For New Design, Please Use The New P409 Series @ 275 VAC |

Specifications

| | |
|-------------------------------|----------|
| Capacitance: | 0.22 uF |
| Capacitance Tolerance: | 20% |
| Voltage AC: | 250 VAC |
| Voltage DC: | 630 VDC |
| Temperature Range: | -40/+85C |
| Rated Temperature: | 85C |
| Insulation Resistance: | 3 GOhms |
| Safety Class: | X2 |