

KEMET Part Number: PMR205AB6220M220R30
(P405QM224M125AH221)

PMR205/P405, Film, Metallized Paper, Resistor/Capacitor, 0.22 uF, 20%, 250 VDC, 85C, Lead Spacing = 15.2mm



| General Information | |
|---------------------|---|
| Supplier: | KEMET |
| Series: | PMR205/P405 |
| Dielectric: | Metallized Paper |
| Style: | Radial |
| Features: | RC Unit not approved |
| RoHS: | Yes |
| Lead: | Wire Leads |
| Construction: | Molded |
| Miscellaneous: | Resistor Tolerance: +/-30%. Resistor= 220 Ohms |

| Dimensions | |
|------------|-----------------|
| L | 18.5mm MAX |
| H | 13mm MAX |
| T | 7.3mm MAX |
| S | 15.2mm +/-0.4mm |
| LL | 30mm +5mm |
| F | 0.8mm +/-0.05mm |

| Specifications | |
|------------------------|----------|
| Capacitance: | 0.22 uF |
| Capacitance Tolerance: | 20% |
| Voltage AC: | 125 VAC |
| Voltage DC: | 250 VDC |
| Temperature Range: | -40/+85C |
| Rated Temperature: | 85C |
| Insulation Resistance: | 3 GOhms |
| Safety Class: | X2 |

| Packaging Specifications | |
|--------------------------|-----------|
| Packaging: | Bulk, Bag |
| Packaging Quantity: | 400 |