

AUTOMATION & CONTROL

ENCLOSURES

POWER

INTERCONNECT

TEST & MEASUREMENT

PASSIVE & ACTIVE

LIGHTING

ASSEMBLY

INDEX

Super Bright LED Work Light — CLN Series



- ▶ Super Bright, 820 lx (@ 1 m), LED (-CD Type) 85 mm Square
- ▶ Tilt Only and Pan and Tilt Versions
- ▶ Daylight White and Warm White Light Colors

- ▶ Rated Input Voltage; 24 VDC
- ▶ IP66G, IP67G for Oily Environments
- ▶ IP69K for High Temperature, High Pressure Wash Down

CLN — Series

Stock No.	Mfr.'s Type	Description	EACH
70276560	CLN-24-CD-T	Super Bright LED Work Light Daylight White-Tilt	239.98
70276561	CLN-24-CL-T	Super Bright LED Work Light Warm White-Tilt	239.98
70276562	CLN-24-CD-PT	Super Bright LED Work Light Daylight White-Pan and Tilt	259.27
70276563	CLN-24-CL-PT	Super Bright LED Work Light Daylight White-Pan and Tilt	259.27

Explosion-Safe — CLN-EX Series

Explosion-Safety: CE Ex II 3 GD; Ex nA IIC T4 Gc; Ex tc IIIC T135°C Dc IP65.

Stock No.	Mfr.'s Type	Description	EACH
70276579	CLN-24-CD-PT-EX	Super Bright LED Work Light, Explosion-Safe, Oil Resistant, Daylight White, Pan and Tilt	518.55

Super Bright LED Work Light — CLK Series

- ▶ Up to 2100 lx (@1 m, CLK-CD)
- ▶ 200 mm, 300 mm, and 600 mm Lengths
- ▶ IP66G, IP67G for Oily Environments
- ▶ IP69K for High Temperature, High Pressure Wash Down
- ▶ Daylight White (All Models) and Natural White Light Colors (Select Models)
- ▶ Aluminum or Stainless Steel Body
- ▶ Leads, M12 QD and Daisy Chain Types Available
- ▶ Rated Input Voltage; 24 VDC
- ▶ Mounting Angles Can Be Adjusted with Optional Swivel Bracket (SZ-320KS)



CLK Series

Stock No.	Mfr.'s Type	Description	EACH
70276564	CLK2S-24AG-CD	Super Bright LED Bar 200 mm Aluminum Tempered Glass	312.35
70276565	CLK3S-24AG-CD	Super Bright LED Bar 300 mm Aluminum Tempered Glass	372.64
70276566	CLK3C-24AG-CD	Super Bright LED Bar 300 mm Aluminum Tempered Glass, M12 QD	444.98
70276567	CLK3CL-24AG-CD	Super Bright LED Bar 300 mm Aluminum Tempered Glass Daisy Chainable	553.53
70276568	CLK6S-24AG-CD	Super Bright LED Bar 600 mm Aluminum Tempered Glass, Leads	686.18
70276569	CLK6C-24AG-CD	Super Bright LED Bar 600 mm Aluminum Tempered Glass M12 QD	758.53
70276570	CLK6CL-24AG-CD	Super Bright LED Bar 600 mm Aluminum Tempered Glass Daisy Chainable	855.02
70276571	CLK3C-24SG-CD	Super Bright LED Bar 300 mm Stainless Steel, Tempered Glass M12 QD	867.07
70276572	CLK3CL-24SG-CD	Super Bright LED Bar 300 mm Stainless Steel, Tempered Glass, Daisy Chainable	953.01
70378232	CLK3C-24SA-CD	Super Bright LED Bar 300 mm Stainless Steel, Tempered Glass Covered with Acrylic Lens, M12 QD	718.99
70378233	CLK3CL-24SA-CD	Super Bright LED Bar 300 mm Stainless Steel, Tempered Glass Covered with Acrylic Lens, Daisy Chainable	814.99

Explosion-Safe — CLK-EX Series

Explosion-Safety: CE Ex II 3 GD; Ex nA IIC T4 Gc; Ex tc IIIC T135°C Dc IP65.


Stock No.	Mfr.'s Type	Description	EACH
70276573	CLK2S-24AG-CD-EX	Super Bright LED Bar 200 mm Explosion-Safe, Oil Resistant, Leads	650.00
70276574	CLK3S-24AG-CD-EX	Super Bright LED Bar 300 mm Explosion-Safe, Oil Resistant, Leads	686.18
70276575	CLK3C-24AG-CD-EX	Super Bright LED Bar 300 mm Explosion-Safe, Oil Resistant, M12 QD	728.38
70276576	CLK6S-24AG-CD-EX	Super Bright LED Bar 600 mm Explosion-Safe, Oil Resistant, Leads	879.13
70276577	CLK6C-24AG-CD-EX	Super Bright LED Bar 600 mm Explosion-Safe, Oil Resistant, M12 QD	915.31
70276578	CLK3C-24SG-CD-EX	Super Bright LED Bar 300 mm Stainless Steel, Explosion-Safe, Oil Resistant, M12 QD	987.65

Bright LED Illumination Light Bar — CLA Series



Stock No.	Mfr.'s Type	LUX*	Length mm (In.)	Color	Rated Voltage	EACH
70038919	CLA1S-24-CD	140	100 (3.9)	Daylight White	24	107.33
70038920	CLA1S-24-CN	140	100 (3.9)	Natural White	24	107.33
70038922	CLA2S-24-CD	270	200 (7.9)	Daylight White	24	130.24
70038923	CLA2S-24-CN	270	200 (7.9)	Natural White	24	130.24
70038924	CLA3S-24-CD	400	300 (11.8)	Daylight White	24	142.31
70038925	CLA3S-24-CN	400	300 (11.8)	Natural White	24	142.31
70038926	CLA3S-24-Y	220	300 (11.8)	Amber	24	142.31
70038927	CLA6S-24-CD	650	600 (23.6)	Daylight White	24	244.80
70038928	CLA6S-24-CN	650	600 (23.6)	Natural White	24	244.80
70038929	CLA9S-24-CD	810	900 (35.4)	Daylight White	24	335.25
70038930	CLA9S-24-CN	810	900 (35.4)	Natural White	24	335.25
70038931	CLA12S-24-CD	890	1200 (47.2)	Daylight White	24	451.02
70038932	CLA12S-24-CN	890	1200 (47.2)	Natural White	24	451.02
70038933	CLA15S-24-CD	945	1500 (59.0)	Daylight White	24	469.95
70038934	CLA15S-24-CN	945	1500 (59.0)	Natural White	24	566.78

*At 50 cm. Amber for CLA3S only.



- ▶ Bright, Long-Life (40K Hours) LED, Lower Power Consumption and Less Heat Generation Than Fluorescent Lamps
- ▶ Protection Rating IP66, IP67, IP69K
- ▶ Rated Voltage DC 24 V, 2.5 W to 28.8 W Consumption
- ▶ Available in Daylight White, Natural White (CLA1S) and Amber (CLA3S only)
- ▶ Applications: Workstations, Enclosures, Semiconductor Machines, General Illumination and Some Vision Applications
- ▶ Units with 3 Meter Cable Also Available

LED Light Strip — CWA Series

Bright and Affordable LED Light Strip

- ▶ Bright Long-Life (40K Hours) LED
- ▶ Lower Power Consumption and Less Heat Generation Than Fluorescent Lamps
- ▶ 180 mA to 540 mA Current Consumption
- ▶ Rated Voltage: 24 VDC
- ▶ Available Daylight White
- ▶ Protection Rating IP65
- ▶ Durable Polycarbonate Construction

- ▶ Applications: Workstations, Enclosures, Semiconductor Machine and General Illumination



Stock No.	Mfr.'s Type	Description	Rated Voltage (Polarized)	EACH
70378223	CWA3S-24-CD	300 mm Long, LED Light Strip, Daylight, 100 lux at 1 m	24 VDC	57.99
70378224	CWA6S-24-CD	600 mm Long, LED Light Strip, Daylight, 200 lux at 1 m	24 VDC	118.99
70378225	CWA9S-24-CD	900 mm Long, LED Light Strip, Daylight, 300 lux at 1 m	24 VDC	158.99

