

KEMET, Z-PWZ, Ferrite Beads, Noise Suppression, 130 mOhms



| Dimensions | |
|------------|-----------------|
| Chip Size | 0603 |
| L | 1.6mm +/-0.1mm |
| W | 0.8mm +/-0.1mm |
| T | 0.8mm +/-0.1mm |
| B | 0.3mm +/-0.15mm |

| Packaging Specifications | |
|--------------------------|------|
| Packaging: | T&R |
| Packaging Quantity: | 4000 |

| General Information | |
|---------------------|----------------------------|
| Series: | Z-PWZ |
| Style: | SMD Chip |
| Description: | Chip Bead, Power Line |
| Features: | For MHz Range Applications |
| RoHS: | Yes |

| Specifications | |
|----------------------|--------------------|
| Impedance: | 330 Ohms (100 mHz) |
| Impedance Tolerance: | 25% |
| Ripple Current: | 900 mA (MAX) |
| Temperature Range: | -40/+125C |
| Resistance: | 0.13 Ohms |