


KEMET, ESD-R-H, EMI Cores, Noise Suppression



| Dimensions | |
|------------|----------------|
| D | 22mm MAX |
| D2 | 7.7mm +/-1.0mm |
| T | 14mm MAX |

| Packaging Specifications | |
|--------------------------|-----------|
| Packaging: | Tray, Box |
| Packaging Quantity: | 480 |
| Weight: | 11.8 g |

| General Information | |
|---------------------|--|
| Series: | ESD-R-H |
| Style: | Round - Snap-on |
| Cable Type: | Round Cable |
| Description: | EMI Core Solid, For Round Cables, Toroidal Cores |
| Features: | High Heat Resistance, Cable Holding Mechanism |
| RoHS: | Yes |
| Qualifications: | UL94V-0 |
| Case Color: | Black |
| Toroidal: | ESD-R-19SD |
| Materials: | Ni-Zn |

| Specifications | |
|----------------------|-------------------------|
| Temperature Range: | -40/+120C |
| Effective Frequency: | 300 MHz (FM Band Range) |