


KEMET Part Number: SS20H-20018 Not for New Design
(UAL20H20018000)

KEMET, SS20H, AC Line Filters, Common Mode, 1800 uH



Dimensions

Dimension	Value
L	22mm MAX
T	22mm MAX
H	18.5mm MAX
LL	3.5mm +/-1mm
S	10mm +/-0.5mm

Packaging Specifications

Weight:	12 g
----------------	------

General Information

Series:	SS20H
Style:	Through-Hole
RoHS:	Yes
Notes:	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous:	Inductance Measurement Condition: 1kHz 1V KC530

Specifications

Voltage AC:	250 VAC
Inductance:	1.8 mH
Current:	2 A
Temperature Range:	-25/+120C
DC Resistance:	110 mOhms