


KEMET, SSHB10H, AC Line Filters, Dual Mode, 2300 uH



Dimensions	
L	22mm MAX
T	17mm MAX
H	15.5mm MAX
LL	3.5mm +/-0.5mm
S	10mm +/-0.5mm

Packaging Specifications	
Packaging:	Tray
Packaging Quantity:	300
Weight:	10 g

General Information	
Series:	SSHB10H
Style:	Through-Hole
RoHS:	Yes
Notes:	Marking: 17 Lot No.
Miscellaneous:	Temperature Rise Maximum: 60 K

Specifications	
Voltage AC:	250 VAC
Inductance:	2.3 mH (10 kHz)
Current:	1.7 A
Temperature Range:	-25/+130C
DC Resistance:	190 mOhms