


KEMET, EFS, Flex Suppressors, Noise Suppression



General Information	
<b>Series:</b>	EFS
<b>Style:</b>	Sheet
<b>Description:</b>	Flex Suppressor Super High Frequency Type
<b>Features:</b>	Super High Frequency
<b>RoHS:</b>	Yes
<b>Qualifications:</b>	UL94 V-0, UL File No. E176124
<b>Environment:</b>	RoHS Compliant, Halogen Free, PVC Free, Lead Free, Red Phosphorus Free

Dimensions	
<b>Sheet Size</b>	240x240mm
<b>L</b>	240mm NOM
<b>W</b>	240mm NOM
<b>T</b>	0.2mm NOM

Specifications	
<b>Temperature Range:</b>	-40/+105C
<b>Magnetic Permeability:</b>	10 u At 3MHz
<b>Effective Frequency:</b>	40 GHz Max
<b>Resistance:</b>	100 MOhms MIN
<b>Specific Gravity:</b>	4.5 Atm TYP

Packaging Specifications	
<b>Weight:</b>	50.1 g