

KEMET, SSHB21H, AC Line Filters, Dual Mode, 0.04 H



| Dimensions | |
|------------|----------------|
| L | 26mm MAX |
| T | 23mm MAX |
| H | 15.5mm MAX |
| LL | 3.5mm +/-0.5mm |
| S | 15mm +/-0.5mm |

| Packaging Specifications | |
|--------------------------|------|
| Packaging: | Tray |
| Packaging Quantity: | 360 |
| Weight: | 14 g |

| General Information | |
|---------------------|--------------------------------|
| Series: | SSHB21H |
| Style: | Through-Hole |
| RoHS: | Yes |
| Notes: | Marking: 06 Lot No. |
| Miscellaneous: | Temperature Rise Maximum: 60 K |

| Specifications | |
|--------------------|----------------|
| Voltage AC: | 250 VAC |
| Inductance: | 40 mH (10 kHz) |
| Current: | 600 mA |
| Temperature Range: | -25/+130C |
| DC Resistance: | 1.5 Ohms |